

1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com



# 7-Port USB 2.0 Hi-Speed Hub

MODEL NUMBER: U223-007











### Description

Tripp Lite's U223-007, 7-port USB 2.0 hub is the most versatile and powerful hub on the market. It allows you to connect up to seven USB devices to a single USB port on your computer. This unit meets or exceeds USB 2.0 Specifications for Hi-Speed data transmission rates up to 480Mbps. Perfect for both the mobile and desktop user. While the hub will function perfectly in virtually all cases without needing external power, a compact, multi-voltage AC adapter (110/220V) has been provided for the rare circumstance when connecting a power hungry device. This USB 2.0 device is backwards compatible so that it will function with both USB 2.0 and USB 1.1 devices. Over-current protection safeguards connected equipment from overvoltages.

#### **Features**

- USB2.0 7-Port Hub
- Supports data transfer rates up to 480Mbps
- Connect up to 7 USB devices to a single USB port on your computer
- Compact design is ideal for use with a laptop/notebook computer
- Does not require external power, software, or complicated set-up procedures
- Plug-and-play/hot-swappable allows you to add or remove a device at any time
- · Per-port overcurrent protection
- Bus-powered or self-powered
- Supports USB 2.0 spec up to 500mA per port
- On bus-power, 500mA from the USB 2.0 computer port is shared between the hub ports
- The included external power supply provides 2.5A of power, to be shared between the hub ports (up to 500mA per port)
- Compact, multi-voltage power supply (110/220V) provided
- · Compatible with all major operating systems

# **Specifications**

## **Highlights**

- Connects up to 7 USB 2.0 devices
- Bus-powered or optional AC adapter
- Compatible with all major operating systems

### **Applications**

 Notebook and Desktop computers where additional USB ports are needed

## **System Requirements**

- USB 2.0 Computer Port
- USB Peripherals

### Package Includes

- U223-007 USB 2.0 Hub
- User's Manual
- USB 2.0 Mini B male to USB 2.0
  A male cable
- 5V/3A DC Power Supply (Optional)





OVERVIEW	
AC Adapter	5V/3A DC Power Supply
Cable Type	USB
ОИТРИТ	
USB Charging	No
PHYSICAL	
Unit Dimensions (hwd / in.)	0.63H x 6.54W x 1.31D
Unit Dimensions (hwd / cm)	1.6 x 16.61 x 3.33
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0°C to +70°C
Operating Humidity Range	10% to 90 % RH (no condensation)
CONNECTIONS	
Connector A	USB A (MALE)
Connector B	USB A (FEMALE) (X7)
Ports	7
SPECIAL FEATURES	
Chromebook Compatible	Yes
CERTIFICATIONS	
Approvals	CE, FCC and RoHS
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: http://www.tripplite.com/products/product-certification-agencies