

## DisplayPort to HDMI Adapter - 4K

StarTech ID: DP2HD4KADAP



This DisplayPort™ to HDMI® adapter supports 4K video resolution, enabling you to connect DisplayPort devices, such as an Ultrabook™ or desktop computer, to a 4K HDMI display or projector.

### Astonishing 4K picture quality

You will be amazed at how this adapter flawlessly manages your graphics-intensive content. With support for resolutions up to 4K - four times the resolution of high-definition 1080p - its lossless performance makes the adapter the ideal solution for high-resource applications such as graphic design, CAD & CAM design, or health care imaging (MRI, radiology diagnostics, etc.).

Plus, the 4K adapter supports 1080p displays, which makes it a great accessory for home, office or other workspace applications.

### Arrive prepared, wherever you go

This DP to HDMI adapter is extremely portable, with a lightweight, small-footprint design. It's the perfect accessory to carry with your Ultrabook, fitting easily into your laptop bag or carrying case. Its ultra-portable design makes the adapter ideal for BYOD (Bring Your Own Device) applications at the office, and enables you to arrive prepared when you're presenting to a potential client, teaching off-site, or traveling to meet with a customer.

The DP2HD4KADAP is backed by a 2-year StarTech.com warranty and free lifetime technical support.

## Applications

- Connect your 4K HDMI display to a DisplayPort output port
- Carry with your laptop for BYOD office applications
- Use an HDMI display as a secondary monitor for your DisplayPort computer

## Features

- Astonishing picture quality four times the resolution of 1080p with support for 4K
- Maximum portability with a small footprint and lightweight design
- Hassle-free setup with plug-and-play installation

### Technical Specifications

Warranty	2 Years
Adapter Style	Adapter
Audio	Yes
Converter Type	Passive
Industry Standards	DPCP (DisplayPort Content Protection) HDCP (High Definition Content Protection) DisplayPort 1.2 HDMI 1.4
Ports	1
Audio Specifications	7.1 Surround Sound
Maximum Digital Resolutions	4K x 2K @ 30 Hz
Supported Resolutions	4k x 2K (Ultra HD) 1920x1200 1920x1080 (1080p) 1280x720 (720p)
Wide Screen Supported	Yes
Connector A	1 - DisplayPort (20 pin) Male Input
Connector B	1 - HDMI (19 pin) Female Output
Humidity	10%~85%RH
Operating Temperature	0°C to 60°C (32°F to 140°F)
Storage Temperature	-10°C to 70°C (14°F to 158°F)
Shipping (Package) Weight	20 g [0.7 oz]
Included in Package	1 - DisplayPort to HDMI adapter

### Certifications, Reports and Compatibility

