



EVO-STIK Adhesive Cleaner

A SOLVENT BASED CLEANER

Date: 15 September 2015

Fact Sheet No.: TDS00087

YOUR SMART ADVANTAGES

- Toluene free
- Suitable for most impervious surface
- Cleans adhesive from equipment

USES

EVO-STIK Adhesive Cleaner is a mixture of solvents for cleaning the residue from solvented adhesives. EVO-STIK Adhesive Cleaner can tackle wet or dry adhesive and even small areas of old adhesive can be removed.

It is ideal for cleaning substrates prior to bonding, in particular rubber, metals and many other impervious surfaces. It is also ideal to clean adhesive from equipment and to remove small dried deposits of contact adhesives from surfaces. It is also possible to dilute EVO-STIK 528 Contact Adhesive and EVO-STIK Impact Adhesive for priming very porous substrates. To prime, dilute 50:50 adhesive and cleaner.

EVO-STIK Adhesive Cleaner is not suitable for use on polystyrene, cellulose paint, vinyl, and rayon fabrics.

PRODUCT CHARACTERISTICS

Colour	Colourless
Form	Mobile liquid
Specific Gravity	0.84 approx.
Composition	Mixture of solvents: Ethyl Acetate, Ketones & Alkanes
Product Code	30811682 250 ml x 12 30811681 5 litres x 1

Storage/Shelf Life	Store for up to 24 months when stored in the original, unopened packaging under dry conditions within the temperature range of +15°C to +30°C.
--------------------	------------------------------------------------------------------------------------------------------------------------------------------------

Odour	Sweet
-------	-------

TYPICAL PERFORMANCE DATA (Approx.)

Flash Point	-25°C
Coverage	5 to 10m ² per litre approx.

DIRECTIONS FOR USE

IMPORTANT: Before using EVO-STIK Adhesive Cleaner refer to the relevant Health & Safety Data Sheet, available at www.bostik.co.uk.

PREPARATION

1. Always test the effects of the cleaner on an unseen or test area to determine its suitability; it may damage some sensitive surfaces.
2. Open any windows and doors to ensure good ventilation. Push down and unscrew to remove cap, puncture silver seal using sharp object such as a screwdriver. Ensure container is properly sealed after use.

APPLICATION

3. Wearing gloves use cloths made into pads and moisten them with the cleaner. Use the pad to wipe over the adhesive to be removed.
4. In the case of rubbers, particularly black rubbers, some of the black may appear on the cloth; this is normal.
5. Always repeat the process with another clean pad moistened with cleaner.
6. For removing larger areas of adhesive it is best to use a new cloth at frequent intervals.



FM 01696
BS EN ISO 9001:2008

Bostik Limited, Common Road, Stafford, ST16 3EH, UK. Tel: +44 (0) 1785 272625 www.bostik.co.uk

Bostik, Evo-Stik & Sealocrete are registered trademarks of Bostik Ltd.

7. The use of a number of washings with small quantities of cleaner is far more efficient than a single large washing.
8. Leave cloths outside until fully dry before disposal.

Removal of Dried Adhesive:

9. Always try to minimise the amount of cleaner used.
10. Therefore attempt to remove the bulk of the material to be cleaned by mechanical means as this will drastically reduce the amount of cleaner required.

N.B This cleaner is not designed to remove old deposits of adhesive from ceilings, walls and floors. The cleaner cannot stay in contact with the adhesive long enough to soften the deposits before the solvent runs away or evaporates.

Priming very Porous Substrates:

11. Only prepare enough for immediate use.
12. Dilute EVO-STIK 528, EVO-STIK 613 or EVO-STIK Impact Adhesive (see separate product data sheets) with an, approximately, equal volume of EVO-STIK Adhesive in a clean container. Dispose of any leftover mixture.
13. Always add cleaner to adhesive, slowly, with gentle stirring.
14. Stir well.

PRECAUTIONS IN USE

Work in a very well-ventilated area and avoid breathing the vapours. Ensure that any source or potential source of ignition is removed / isolated.

Always test the effects of the cleaner on an unseen or test area to determine its suitability; it may damage some sensitive surfaces.

Always try to use the minimum amount of cleaner/solvent.

Always wear gloves and safety glasses.

EVO-STIK Adhesive Cleaner is not suitable for use on polystyrene, cellulose paint, vinyl, and rayon fabrics.

For any application not covered please contact Technical Services on +44 (0)1785 272625 or visit www.bostik.co.uk for advice.

Recommendations and suggestions are for guidance only, since conditions of use are completely beyond our control.

For health and safety instruction, first aid measures and spillage and disposal instructions, see separate Health and Safety Data Sheet for EVO-STIK Adhesive Cleaner, available at www.bostik.co.uk.



BOSTIK HOTLINE

Smart help +44 (0) 1785 272625



FM 01696
BS EN ISO 9001:2008

This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products.

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, nor its liability for fraud, or fraudulent misrepresentation, nor any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company.

Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products, and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number in the top right hand corner on the front of this document.

Sales	Tel: 0844 371 1192	Fax: 01785 241818	customer.service@bostik.com
Technical Advice	Tel: 0844 371 1197	Fax: 01785 272867	technical.service@bostik.com
Technical Data & COSHH (MSDS) Data Sheets	Tel: 01785 272625	Fax: 01785 212962	stafford.gatehouse@bostik.com



FM 01696
BS EN ISO 9001:2008

Bostik Limited, Common Road, Stafford, ST16 3EH, UK. Tel: +44 (0) 1785 272625 www.bostik.co.uk
Bostik, Evo-Stik & Sealocrete are registered trademarks of Bostik Ltd.