

Full Motion Universal Ceiling Mount for Projectors

MODEL NUMBER: DUNVPJT



Highlights

- Universal design that fits most projector brands
- Integrated ball joint allows 360-degree full motion rotation and 20-degree tilt for multi-angle viewing
- Four adjustable support arms fit a wide range of mounting holes
- Load capacity up to 55 lbs.

Package Includes

- DUNVPJT Full Motion Universal Ceiling Mount for Projectors
- Mounting Hardware
- Owner's Manual

Description

Tripp Lite's VESA-compliant DUNVPJT Universal Projector Mount features a ceiling plate, ball-and-socket design, multi-directional positioning for proper image alignment and pre-installed security hardware at every connection point. With a universal design that fits most projector brands, the DUNVPJT is perfect for use in classrooms, boardrooms, hotels, bars, restaurants or anywhere a projector needs to be mounted. It offers flexible projector positioning with four adjustable support arms that fit a wide range of mounting holes. Its integrated ball joint allows 360-degree rotation and 20-degree tilt for multi-angle viewing. It has an easy grip knob that holds the image position without any sag or drift. The quick release connector allows the projector to be installed quickly and then easily released for maintenance, without re-alignment. The DUNVPJT supports weights up to 55 lbs. and comes with all necessary mounting hardware.

Features

VESA-compliant Universal Design

- Universal projector mount featuring a ball-and-socket design for multi-directional positioning
- Fits most projector brands
- VESA-compliant

Load Capacity

- Weights up to 55 lbs.

Multi-directional Positioning

- Integrated ball joint allows 360-degree full motion rotation and 20-degree tilt for multi-angle viewing
- Easy grip knob holds the image position without any sag or drift
- Four adjustable support arms fit a wide range of mounting holes
- A quick release connector allows the projector to be installed quickly and then easily released for maintenance, without re-alignment

Security

- Pre-installed security hardware at every connection point

Installation



- All necessary mounting hardware is included

Specifications

PHYSICAL	
Mounting Location	Ceiling
Unit Dimensions (hwd / in.)	5.31 x 5.90 x 19.68
Unit Dimensions (hwd / cm)	13.9 x 15.0 x 49.9
Unit Weight (lbs.)	3.61
Unit Weight (kg)	1.64
Material of Construction	Steel
Color	Black
Screen Size Compatibility (in.)	Universal
Screen Size Compatibility (cm)	Universal
Motion	Full
Degrees of Motion	360-degree full motion rotation; 20-degree tilt
Maximum Weight Capacity (lbs.)	55
Maximum Weight Capacity (kg)	24.95
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
WARRANTY	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>