

## Micro-USB Cable with Right-Angled Connectors - M/M - 1m (3ft)

StarTech ID: *USB2AUB2RA1M*



This Micro-USB cable features two right-angled connectors that let you connect to hard-to-reach ports and also help prevent cable and port damage. The cable is great for charging your mobile devices in a car, or for connecting to peripherals that may be difficult to connect to when using a straight connection.

### Connect to hard-to-reach ports

The right-angled connectors allow you to connect to ports that may otherwise be inaccessible or difficult to reach. Perfect for charging car-mounted mobile devices or for connecting your portable hard drive or other Micro-USB 2.0 device to your computer in such a way that it fits your installation needs.

The angled connectors prevent the cable from bending awkwardly or from straining too much to make a connection. It offers a more natural fit at the connection points, preventing unnecessary stress and damage to the cable and ports.

### Charge and sync your USB 2.0 mobile devices

Replace the cable that came with your Micro USB mobile device, or keep one as a spare while traveling so that your mobile devices will be ready to use while you're on the road.

### Connect to your mobile devices with ease

The cable features a thin, yet sturdy connector molding, so you'll be able to connect to your phone or tablet without removing its protective case. Plus, the cable's right-angled Micro-USB connector lets you text, work or game on your mobile device even while it's charging, without the cable getting in the way.

The USB2AUB2RA1M 1-meter cable is backed by StarTech.com's lifetime warranty for guaranteed reliability.

## Applications

- Charge and sync your Micro-USB mobile devices
- Connect your Micro-USB 2.0 devices, such as an external hard drive, to your PC or laptop

## Features

- Connect to your device and your computer or charger even in hard to reach areas and tight spaces
- Position your USB 2.0 devices as needed throughout your workspace
- Guaranteed reliability with our lifetime warranty

## Technical Specifications

Warranty	Lifetime
Cable Length	1 m [3.3 ft]
Color	Black
Connector Style	Right Angled
Product Length	1 m [3.3 ft]
Product Weight	25 g [0.9 oz]
Wire Gauge	24/30 AWG
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Connector Plating	Nickel
Type and Rate	USB 2.0 - 480 Mbit/s
Connector A	1 - USB A (4 pin) Male
Connector B	1 - USB Micro-B (5 pin) Male
Package Quantity	1
Shipping (Package) Weight	31 g [1.1 oz]
Included in Package	1 - 1m Right-Angled Micro USB 2.0 Cable

## Certifications, Reports and Compatibility

