

USB 3.0 Data Transfer Cable for Mac and Windows

StarTech ID: USB3LINK



Here's an easy way to transfer files from your old computer to your new one. This data transfer cable lets you move files quickly over USB 3.0, and works with both Mac and Windows®.

Save time setting up your new computer

The transfer cable saves you time and effort when you're upgrading to a new computer. You can transfer your files and settings quickly over USB 3.0, also known as USB 3.1 Gen 1, with file transfer speeds up to 5 Gbps. Plus, there are no additional drivers to install when connecting your computers, because the necessary software is stored on the cable.

Wide compatibility with Mac and PC

The USB 3.0 transfer cable lets you transfer files between two computers including Windows to Windows, Windows to Mac, Mac to Windows, and even Mac to Mac.

The data transfer cable is compatible with Windows Easy Transfer software for migrating to newer versions of Windows, up to Windows 8. Through PCLinq, the transfer cable supports Windows 8.1. The built-in PCLinq software also allows file transfers in any direction between any compatible operating systems. The data transfer cable supports Mac OS 10.7.5 to 10.10, Windows XP, Vista, 8 and 7, and Windows 8.1 (with PCLinq).

The USB3LINK data transfer cable comes in a convenient 2 m (6 ft.) length, and is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- When you upgrade to a new computer, transfer files and settings from your older PC or Mac
- An easy solution for transferring documents, photos, music and other files to your new computer
- Use it with Mac OSX 10.x, Mac OS X and Windows 7, 8, Vista and XP with no CD or download required

Features

- Transfer files from your old computer to your new computer quickly over USB 3.0 (5 Gbps)
- Mac and PC compatible - Mac OS 10.7.5 to 10.10, Windows XP, Vista, 8 and 7, and Windows 8.1 (with PCLinq)
- Compatible with Windows Easy Transfer software for migrating to newer version of Windows (up to Windows 8)
- PCLinq software for file transfer in any direction between any compatible OS
- Software is stored on cable - no CD or download required
- Convenient 2m cable length

Technical Specifications

Warranty	2 Years
Color	Black
Enclosure Type	Plastic
Product Height	0.5 in [11.5 mm]
Product Length	72.8 in [1850 mm]
Product Weight	2.5 oz [72 g]
Product Width	0.9 in [24 mm]
Chipset ID	Prolific - PL27A1
Ports	1
Maximum Data Transfer Rate	5 Gbps
MTBF	500,000
Type and Rate	USB 3.0 - 5 Gbit/s
Connector Type(s)	1 - USB 3.0 A (9 pin; SuperSpeed)
OS Compatibility	Windows® 10 (32/64), 8 / 8.1 (32/64), 7 (32/64), Vista (32/64), XP (32/64) Mac OS® 10.7.5 and later (tested up to 10.11)

Note: The provided PCLInq software is required in Windows 10, 8.1, and Mac OS. In Windows 10 and 8.1, Microsoft removed support for cables from the Windows Easy Transfer software.

LED Indicators	2 - Link/Activity
Humidity	5%RH ~ 85%RH
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Shipping Weight (Package)	4.7 oz [132 g]
Included in Package	1 - USB 3.0 Transfer Cable
Included in Package	1 - Instruction Manual

Package

Certifications, Reports and Compatibility

