


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0347930081](#)
Status: **Active**
Overview: [Mini50™ Connection Systems](#)
Description: Mini50™ Unsealed Right Angle Header, Single Row, 8 Circuit, Polarization Option B, Gray, Tray

Documents:

| | |
|--|---|
| 3D Model | Application Specification AS-34791-020-CH (PDF) |
| Drawing (PDF) | Application Specification AS-34791-020-FR (PDF) |
| Product Specification PS-34791-020 (PDF) | RoHS Certificate of Compliance (PDF) |
| Application Specification AS-34791-020 (PDF) | |



Series image - Reference only

General

| | |
|----------------|--|
| Product Family | PCB Headers |
| Series | 34793 |
| Application | Power, Signal, Wire-to-Board |
| Overview | Mini50™ Connection Systems |
| Product Name | Mini50™ |
| UPC | 884982492943 |

Physical

| | |
|--------------------------------|-----------------|
| Breakaway | No |
| Circuits (Loaded) | 8 |
| Circuits (maximum) | 8 |
| Color - Resin | Gray |
| First Mate / Last Break | No |
| Glow-Wire Compliant | No |
| Guide to Mating Part | No |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Tin over Nickel |
| Material - Plating Termination | Tin over Nickel |
| Material - Resin | Polyester Alloy |
| Net Weight | 1.714/g |
| Number of Rows | 1 |
| Orientation | Right Angle |
| PC Tail Length | 2.90mm |
| PCB Locator | Yes |
| Packaging Type | Tray |
| Pitch - Mating Interface | 2.00mm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Temperature Range - Operating | -40°C to +105°C |
| Termination Interface: Style | Through Hole |

Electrical

| | |
|-------------------------------|---------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 500V DC |

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|--|
| Application Specification | AS-34791-020, AS-34791-020-CH, AS-34791-020-FR |
| Product Specification | PS-34791-020 |
| Sales Drawing | SD-34793-001 |

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

China RoHS

Not Relevant

Compliant

Search Parts in this Series

[34793 Series](#)

Mates With

[34791 Mini50™ Unsealed Single Row Receptacle](#)

This document was generated on 03/04/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION