




# Mighty Cam Eidos

Integrated 2M Camera / 11.6" Monitor

## Inspection Simplified

Aven's **Mighty Cam Eidos** combines a 2 megapixel inspection camera with an 11.6" 1080p monitor. Create your own all-in-one inspection system by attaching the Eidos to any C/CS mount microscope or video lens system. **Includes a SD card port** for image and video capture, no computer required.

For applications requiring imaging or measurement software, Aven has included a **USB output**, making the Eidos the most versatile inspection camera available on the market.



SD Card Slot. Save high resolution images and videos with no need for a PC

MIGHTY CAM EIDOS 2M CAMERA / 11.6" MONITOR	
<b>IMAGE SENSOR</b>	CMOS 1920*1080 FULL HD Panasonic 1/2.8"
<b>OUTPUT</b>	USB 2.0
<b>PIXEL SIZE</b>	2.75*2.75um
<b>LCD</b>	11.6" 1080p Resolution IPS Panasonic LCD
<b>WHITE BALANCE</b>	Automatic/Manual
<b>SCAN TYPE</b>	Progressive Scan
<b>LENS MOUNT</b>	C Mount
<b>FRAME RATE</b>	60FPS
<b>SCREEN SIZE</b>	11.6"
<b>WEIGHT</b>	2.025lbs
<b>PHOTO FORMAT</b>	JPEG
<b>SHUTTER</b>	Adjustable
<b>COLOR</b>	RGB
<b>PACKAGE CONTENTS</b>	Mighty Cam Eidos USB Cable Wireless Mouse with USB Bluetooth connection

Connects to any trinocular microscope or video lens with a C/CS mount. No need to connect to an external monitor.



USB output connects to any computer for measurement and imaging software.

Part #	Description	Sensor
<b>26100-260</b>	<b>Mighty Cam Eidos</b>	<b>CMOS</b>



# Mighty Auto Focus


Auto Focus 2M Inspection Camera

## Instant Auto Focus

2M auto focus inspection camera. Achieve instant and accurate focus without the need to constantly adjust your lens. Ideal for inspecting multilayered objects such as PCBs. View crystal clear 1080p images on your HD monitor. Compatible with any C/CS mount microscope or video lens.

Built-in features include:

- Auto/Manual Focus
- Exposure
- White Balance
- Horizontal/Vertical Color Line Grids
- Brightness/Contrast/Sharpness settings
- Freeze Frame



HDMI Output connects to any HD monitor. View crystal-clear 1080p HD images.

MIGHTY CAM EIDOS 2M CAMERA / 11.6" MONITOR	
<b>IMAGE SENSOR</b>	CMOS 1920*1080 FULL HD Panasonic 1/2.8"
<b>OUTPUT</b>	USB 2.0
<b>PIXEL SIZE</b>	2.75*2.75um
<b>WHITE BALANCE</b>	Automatic/Manual
<b>LENS MOUNT</b>	C Mount
<b>FRAME RATE</b>	60FPS
<b>FOCUS</b>	Auto / Manual
<b>WEIGHT</b>	2.025lbs
<b>FILE FORMAT</b>	JPEG / MP4
<b>SHUTTER</b>	Adjustable
<b>COLOR</b>	RGB
<b>PACKAGE CONTENTS</b>	Mighty Cam Eidos USB Cable Cable Wired Remote Control

Connects to any trinocular microscope or video lens with a C/CS mount.



Remote control with clearly labeled buttons.

Part #	Description	Sensor
26100-257	Mighty Cam Auto Focus	CMOS