



Fig. 1



Fig. 2



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8



Fig. 9



Fig. 11

ESD/Static Protection

Retail Part No.	Figure No.	Description	Features
20-8004	1	Medium to Large Wrist Strap	10' Coil Cord, Banana Plug/Alligator Clip, 1 meg Ohm Resistance for Safety
12-8012	1	GC Professional Adjustable Wrist Strap Kit	10' Coil Cord, 4 mm Snap Stud and Alligator Clip
12-8013	1	Wrist Strap Only	for 12-8012
12-8020	1	Coil Cord Only	for 12-8012
12-8010	1	Adjustable Economy Wrist Strap Kit	6' Coil Cord, 4 mm Snap Stud and Alligator Clip
12-8011	1	Wrist Strap Only	for 12-8010
12-8055	3	Combination Wrist Strap/Footwear Tester	Indicates Low-pass or High Results
12-8056		Combination Tester/Adapter	for 12-8055
12-8057		Stand and Baseplate	for 12-8055
12-8058		Footplate and Cord	for 12-8055
12-8050	4	Touch Type on Demand Wrist Strap Tester	Tests the Entire Circuit
12-8051		AC Adapter	for 12-8050
12-8024	5	Ground Cords for Floormats with 10 mm Studs	10' Yellow Striped Green Ground Cord, Terminated w/#10 (200") Ring Terminal
12-8026	5	Ground Cords for Floormats with 10 mm Studs	Custom Tailor Installation (No Workstation)
12-8028	6	2 Pack, 10 mm Snap Sockets	for 12-8026
12-8029	6	2 Pack, 3/8" Push and Clinch 10 mm Snap Stud	
12-8034	6	2 Pack, 10 mm Snap Socket Adapter	for Use with ESD Grounding Mats, Adapts 10 mm Socket to 10 mm Socket
12-8030	7	Dual Bench Mount	2 Person Grounding
12-6960	8	Anti-Static Wrist Strap	Conductive Velcro Band Made of Nylon and Coated on Inside with Conductive Carbon
12-8042	9	Dissipative Workstation Kit	Blue Bench Mat and Common Point Ground Cord
12-8043	9	ESD Two Layer Workstation Mat (24" x 40')	Use in Soldering or Assembly Area
12-8044	9	Two Layer Workstation Kit (18" x 24")	Common Ground Point with 12-8028
12-8045	9	ESD Three Layer Workstation Mat (24" x 40')	Use in Soldering or Assembly Area
12-8060	11	Touch Type Wrist Strap Tester	AC Operation, Operates on Demand, Common Point Grounding Jacks for 2 Straps

Tools