




Mighty Vue Pro 5D ESD Safe Magnifying Lamp

with color temperature control



7.5 Inch x 6.2 inch/ 5 Diopter Lens
2.25x Magnification



Color Temperature Range: 3500K - 6500K
Illumination: Max 1100lm



Heavy-Duty
Mounting Clamp



Aven's **MightyVue Pro** LED series magnifying lamps are in a class of their own. Featuring adjustable color temperature (3500K-6500K), brightness control (max 1100lm), in addition to an attractive design, the Mighty Vue Pro series lamps are the most advanced available.

- Touch-sensitive brightness and color temperature controls
- Large 7.5 x 6.2 inch, 5-Diopter crystal-clear glass lens for distortion-free viewing
- 36 inch spring-balanced arm ensures a large working range
- 360° swivel motion allows the head to be placed in any position
- Covered spring arm prevents pinching hazards
- ESD Safe coating

MIGHTY VUE PRO 5D ESD SAFE	
MAGNIFICATION	2.25X (5-Diopter)
LENS DIAMETER	7.5in x 6.2in
ADJUSTABLE ARM LENGTH	36in
COLOR	Black
LIGHTING	60 LED Lights
ESD Safe	Yes

Part #	Description	Lens
26505-ESL-X15	Mighty Vue Deluxe LED Magnifying Lamp	5 Diopter




Mighty Vue Pro 3 Diopter Magnifying Lamp

with color temperature control



7.5 Inch x 6.2 inch/ 3 Diopter Lens
1.75x Magnification



Color Temperature Range: 3500K - 6500K
Illumination: Max 1100lm



Heavy-Duty
Mounting Clamp



Aven's **MightyVue Pro** LED series magnifying lamps are in a class of their own. Featuring adjustable color temperature (3500K-6500K), brightness control (max 1100lm), in addition to an attractive design, the Mighty Vue Pro series lamps are the most advanced available.

- Touch-sensitive brightness and color temperature controls
- Large 7.5 x 6.2 inch, 3-Diopter crystal-clear glass lens for distortion-free viewing
- 36 inch spring-balanced arm ensures a large working range
- 360° swivel motion allows the head to be placed in any position
- Covered spring arm prevents pinching hazards

MIGHTY VUE PRO 3 DIOPTER MAGNIFYING LAMP	
MAGNIFICATION	1.75x (3 Diopter)
LENS DIAMETER	7.5in x 6.2in
ADJUSTABLE ARM LENGTH	36in
COLOR	Black
LIGHTING	60 LED Lights
ESD Safe	No
Item Number	26505-LED-XL3