

Pre-Printed Warning Header Labels (B-483)

White polyester thermal transfer material with glossy finish and aggressive adhesive specifically designed for powder coated surfaces.




Figure 72
(Includes pre-printed header)



Fits Printer Model(s)	Diagram	Catalog #	B#	Material	Header	Label Height A Inch (mm)	Label Width B Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
TLS, BMP71*	Fig. 72	PTL-37-483-WARNING	B-483	Polyester	WARNING	3.000 (76.2)	1.900 (48.3)	1	100	R6010
TLS, BMP71*	Fig. 72	PTL-38-483-WARNING	B-483	Polyester		4.000 (101.6)	1.900 (48.3)	1	100	R6010

Faceplate, Outlet and Port Labels (B-412, B-422)

Thick polypropylene material used for equipment identification. Offers high print legibility and high tensile strength.




Figure 28




Figure 55



Fits Printer Model(s)	Diagram	Part Number	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
TLS, BMP71*	Fig. 28	PTL-55-412	B-412	Non-adhesive Strip	White	0.230 (5.8)	50 ft. (15.2 m)	1	1 Roll Cont.	R6210
TLS, BMP71*	Fig. 28	PTL-56-412	B-412	Non-adhesive Strip	White	0.375 (9.5)	50 ft. (15.2 m)	1	1 Roll Cont.	R6210
TLS, BMP71*	Fig. 28	PTL-57-412	B-412	Non-adhesive Strip	White	0.500 (12.7)	50 ft. (15.2 m)	1	1 Roll Cont.	R6210
TLS, BMP71*	Fig. 28	PTL-58-412	B-412	Non-adhesive Strip	White	0.535 (13.6)	50 ft. (15.2 m)	1	1 Roll Cont.	R6210
TLS, BMP71*	Fig. 28	PTL-59-412	B-412	Non-adhesive Strip	White	0.785 (19.9)	50 ft. (15.2 m)	1	1 Roll Cont.	R6210
TLS, BMP71*	Fig. 55	PTL-40-412	B-412	Non-adhesive Strip	White	1.938 (49.2)	0.375 (9.5)	1	750	R6210
TLS, BMP71*	Fig. 55	BM71-40-412	B-412	Non-adhesive Strip	White	1.938 (49.2)	0.375 (9.5)	1	5000	R6210
TLS, BMP71*	Fig. 33	PTL-46-422	B-422	Adhesive Strip	White	0.375 (9.5)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
TLS, BMP71*	Fig. 33	PTL-8-422	B-422	Adhesive Strip	White	0.500 (12.7)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
TLS, BMP71*	Fig. 34	PTL-39-422	B-422	Polyester Individual Labels	White	0.375 (9.5)	0.600 (15.2)	1	750	R6010
TLS, BMP71*	Fig. 29	PTL-7-422	B-422	Polyester Individual Labels	White	0.500 (12.7)	0.500 (12.7)	1	500	R6010
TLS, BMP71*	Fig. 29	PTL-16-422	B-422	Polyester Individual Labels	White	1.000 (25.4)	0.375 (9.5)	1	500	R6010
TLS, BMP71*	Fig. 29	PTL-17-422	B-422	Polyester Individual Labels	White	1.000 (25.4)	0.500 (12.7)	1	500	R6010

Non-Adhesive Polyethylene Tag Material (B-109)

Excellent multi-purpose tag for identifying multiconductor cables, inventory, safety warning repair and work-in-processing manufacturing. Good weatherability, humidity resistance and legibility after solvent exposure.




Figure 45




Figure 56



Fits Printer Model(s)	Diagram	Part Number	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
TLS, BMP71*	Fig. 45	PTL-36-109	B-109	Polyethylene	White	1.125 (28.6)	1.750 (44.5)	1	250	R4310
TLS, BMP71*	Fig. 56	PTL-12-109	B-109	Polyethylene	White	3.000 (76.2)	0.750 (19.1)	1	100	R4310
TLS, BMP71*	Fig. 56	BM71-12-109	B-109	Polyethylene	White	3.000 (76.2)	0.750 (19.1)	1	1000	R4310

See all TLS2200® and PC Link™ Ribbon parts on page 323.

* Yellow media adaptor required for use in the BMP®71 printer. See page 324.

