

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1721590608](#)  
**Status:** **Active**  
**Overview:** EdgeMate™ Wire-to-Edge-Card Power Connector  
**Description:** 3.96mm Pitch EdgeMate™ Wire-to-Board Edge Card Connector, Female, Nylon 6/6, White, UL94-V2, with Positive Lock, 8 Circuits

**Documents:**

[3D Model](#) [Packaging Specification PK-172159-0001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-172160-0001 \(PDF\)](#)

**Agency Certification**

UL E29179

**General**

Product Family Edge Card Connectors  
 Series [172159](#)  
 Circuit Size Range 1-64 Circuits  
 Comments See Product Specification for maximum current rating by wire AWG and terminal material.  
 Component Type Edgecard to Wire  
 Data Rate Unrated  
 Edge Card Thickness N/A  
 High Power Bay (30.0A or more) No  
 Orientation Right Angle  
 Overview [EdgeMate™ Wire-to-Edge-Card Power Connector](#)  
 Product Name EdgeMate™  
 Standard Based General  
 UPC 887191569956

**Physical**


(p)ower-(s)ignal Configuration 8p - 0s  
 Circuits (Loaded) 8  
 Circuits (maximum) 8  
 Color - Resin White  
 Durability (mating cycles max) 25  
 Entry Angle 90° Angle  
 Flammability 94V-2  
 Keying to Mating Part Yes  
 Material - Plating Mating N/A  
 Material - Resin Nylon  
 Net Weight 3.200/g  
 PCB Locator Yes  
 PCB Retention Yes  
 PCB Thickness - Recommended 1.57mm  
 Packaging Type Bag  
 Panel Mount No  
 Pitch - Mating Interface 3.96mm  
 Polarized to Mating Part Polarizing Ribs  
 Temperature Range - Operating -40°C to +105°C, -40°C to +80°C  
 Termination Interface: Style Straddle Mount-Edge Card

**Electrical**

Current - Maximum per Contact 7.0A  
 Voltage - Maximum 250V

**Solder Process Data**

Lead-freeProcess Capability N/A



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/79/2015 (17  
 December 2015)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

[172159](#) Series

**Mates With**

Edge Card PCB

**Use With**

[172160](#)

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification

PK-172159-0001

Product Specification

PS-172160-0001

Sales Drawing

SD-172159-0002

This document was generated on 03/01/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**