

### General Information

|                        |  |
|------------------------|--|
| Extended Product Type: | CP1-10W-20   |
| Product ID:            | 1SFA619100R1025  |
| EAN:                   | 7320500240823  |
| Catalog Description:   | PUSHBUTTON#CP1-10W-20  |
| Long Description:      | Compact Pushbutton - Momentary - Flush - White - Non-illuminated - Black plastic - 2NO |

### Categories

Products » Low Voltage Products and Systems » Control Products » Pilot Devices » Pilot Devices - Compact Range

### Ordering

|                         |               |
|-------------------------|---------------|
| EAN:                    | 7320500240823 |
| Minimum Order Quantity: | 10 piece      |
| Customs Tariff Number:  | 85369001      |

### Dimensions

|                     |          |
|---------------------|----------|
| Product Net Width:  | 0.030 m  |
| Product Net Height: | 0.030 m  |
| Product Net Depth:  | 0.055 m  |
| Product Net Weight: | 0.022 kg |

### Container Information

|                               |          |
|-------------------------------|----------|
| Package Level 1 Units:        | 10 piece |
| Package Level 1 Width:        | 0.1 m    |
| Package Level 1 Height:       | 0.03 m   |
| Package Level 1 Length:       | 0.1 m    |
| Package Level 1 Gross Weight: | 0.022 kg |
| Package Level 2 Units:        | 10       |

### Environmental

|              |   |
|--------------|---|
| RoHS Status: | Following EU Directive 2002/95/EC August 18, 2005 and amendment |
|--------------|---|

### Additional Information

|  |   |
|--|---|
| Actuator Type:                                     | Flush   |
| Bezel Material:                                    | Black plastic   |
| Block:   | 2NO   |
| Color:   | White   |
| Degree of Protection:                              | acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20 |
| Function:  | Momentary   |
| IIT Publishing Status:                             | Level 0 - Information enabled                                     |
| Illumination:                                      | Non-illuminated   |
| Mechanical Durability:                             | 0.5 million   |
| Number of Auxiliary Contacts NO:                   | 2   |
| Product Main Type:                                 | CP1   |
| Product Name:                                      | Pushbutton  |
| Product Range:                                     | Compact   |
| Product Type:                                      | CP  |
| Rated Frequency (f):                               | Supply Circuit 50 Hz<br>Supply Circuit 60 Hz                      |
| Rated Operational Current AC-15 (I <sub>e</sub> ): | (220 / 240 V) 1 A<br>(24 / 127 V) 1.5 A                           |
| Rated Operational Current DC-13 (I <sub>e</sub> ): | (125 V) 0.2 A<br>(24 V) 0.3 A                                     |
| RoHS Date:   | 0626 5  |

### Certificates and Declarations (Document Number)

|                                    |                 |
|------------------------------------|-----------------|
| Data Sheet, Technical Information: | 1SFC151003C0201 |
| Declaration of Conformity - CE:    | 1SFA1-70        |
| RoHS Information:                  | 1SFC151012D0202 |

### Classifications

**E-nummer:** 3711274

**ETIM 4:** EC002024 - Accessories for control circuit devices

**ETIM 5:** EC002024 - Accessories for control circuit devices

**Object Classification Code:** S

**UNSPSC:** 39121512

---

