

Product Description:

The complete GU10 range of compact fire rated downlights are perfect for a wide range of applications and installations. Available in fixed, adjustable, IP65 rated and various colour finishes, the range utilises patented integrated intumescent material completely sealing the downlight and cut-out in the event of a fire. Tested in 30, 60 and 90-minute fire rated ceilings, this range is also acoustic rated, providing state of the art sound insulation.

Product Image:



Product Features:

- Loop in/out terminal block for quick and easy installation
- Designed and tested to meet Fire Rating Standards (30, 60, 90-minute fire rated ceilings) for safety and reassurance: BS EN 1365-2: 2014
- Designed and tested to meet acoustic rating standards for reduced sound transmission between separating floors: BS EN ISO 10140-2: 2010 & BS EN ISO 10140-3: 2010 + A1: 2015
- 3 year warranty

GU10 Fixed Lock Ring Aluminium Fire Rated Downlight

Product Specs:

Lamp Base	GU10	Input Voltage	240~240V AC
Input Frequency	50/60HZ	IP Rating	IP20
Fire Protection	Yes	Acoustic Rated	Yes
Height (mm)	110	Cutout Diameter (mm)	75
Overall Diameter (mm)	87	Overall Height (mm)	110
Recess Depth (mm)	110		

SKU Table and Ordering

Cat No.(SKU Code)	Wattage	Lumens	Lumens/Watt	Colour	Ra	Beam Angle
EN-FD101PC						
EN-FD101SN						
EN-FD101W						
EN-FD101PC/30	5W	500lm	100	3000K	80	60°
EN-FD101W/30	5W	500lm	100	3000K	80	60°
EN-FD101SN/30	5W	500lm	100	3000K	80	60°

Compliance & Approvals:



Warranty

Please contact Aurora for specifics concerning warranty on this product. The warranty is invalid in the case of improper use, installation, tampering, and removal of the Q.C. date label; installation in an improper working environment or installation not according to the current edition of the National Electric Code. Should this product fail during the warranty period it will be replaced free of charge, subject to the correct installation of the original product and subsequent return of the faulty unit. Aurora does not accept responsibility for any installation costs associated with the replacement of this product and Aurora reserves the right to alter specifications without prior notice.

UK Enlite Sales

16 Alban Park Hatfield Road St. Albans
AL4 0JJ

United Kingdom

Tel : +44 (0) 1727 83 66 11

Fax : +44 (0) 1727 83 66 22

UK Enlite Distribution

Apex Park 6 Little Burrow Welwyn
Garden City AL7 4SW

United Kingdom

Tel : +44 (0) 1707 35 18 20

Fax : +44 (0) 1727 35 18 21