

Product Description:

Performance - that's what the Uni-Fit™ range of commercial downlights stands for. Featuring ThermoTec™ technology, integrated driver and high quality LED chips to deliver serious lumen performance. The Uni-Fit™ range is the ideal cost effective solution for new or existing installations where traditional compact fluorescent downlights need upgrading to more efficient LED technology.

Product Image:




Product Features:

- Multiple sizes and wattages available to suit all new and retrofit installation lighting requirements
- ThermoTec™ technology utilises a combination of highly efficient LED light source, aluminium heat sinking and thermoplastic material for longer life and consistent performance
- Compact integrated driver for easy installation and shallow ceiling voids
- Life not affected by frequent switching e.g. when used with occupancy controls
- IP44 rated - ideal for use in commercial offices, educational, council buildings and public toilets
- Pre-wired with 500mm 2 core cable
- 1.5kV surge protection
- 3 year warranty

23W Integrated IP44 Non-Dimmable LED Downlight

Line Drawing Image



Product Specs:

Technology	LED	Number of LEDs	60
Luminaire Distribution	Direct	Lifetime L70 (hrs)	25000
Input Voltage	220~240V AC	Input Frequency	50/60HZ
Surge Protection (kV)	1.5	Power Factor	0.9
Dimmable	No	IP Rating	IP44
Cutout Diameter (mm)	170	Overall Diameter (mm)	200
Overall Height (mm)	60	Recess Depth (mm)	70

SKU Table and Ordering

Cat No.(SKU Code)	Wattage	Lumens	Lumens/Watt	Colour	Ra	Beam Angle	SDCM
EN-DL23/30	23W	1750lm	76.09	3000K	80	100°	6
EN-DL23/40	23W	1800lm	78.26	4000K	80	100°	
EN-DL23/64	23W	1850lm	80.43	6400K	80	100°	

Compliance & Approvals:



Warranty

Please contact Aurora for specifics concerning warranty on this product. The warranty is invalid in the case of improper use, installation, tampering, and removal of the Q.C. date label; installation in an improper working environment or installation not according to the current edition of the National Electric Code. Should this product fail during the warranty period it will be replaced free of charge, subject to the correct installation of the original product and subsequent return of the faulty unit. Aurora does not accept responsibility for any installation costs associated with the replacement of this product and Aurora reserves the right to alter specifications without prior notice.

UK Enlite Sales

16 Alban Park Hatfield Road St. Albans
AL4 0JJ

United Kingdom

Tel : +44 (0) 1727 83 66 11

Fax : +44 (0) 1727 83 66 22

UK Enlite Distribution

Apex Park 6 Little Burrow Welwyn
Garden City AL7 4SW

United Kingdom

Tel : +44 (0) 1707 35 18 20

Fax : +44 (0) 1727 35 18 21