


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2005280080](#)
Status: **Active**
Overview: FFC-FPC (SMT)
Description: 1.00mm Pitch Easy-On™ Type FFC/FPC Connector, 1.90mm Height, Double Bottom Contact Type (FD19 Series), Right Angle, Surface Mount, ZIF, 8 Circuits

Documents:

[3D Model](#) [Packaging Specification 2005289200 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification 2005280000 \(PDF\)](#)



General

| | |
|----------------|-------------------------------|
| Product Family | FFC/FPC Connectors |
| Series | 200528 |
| Comments | Black Actuator |
| Overview | FFC-FPC (SMT) |
| Product Name | Easy-On™ |
| UPC | 889056681681 |

Physical

| | |
|--------------------------------|------------------------|
| Circuits (Loaded) | 8 |
| Circuits (maximum) | 8 |
| Color - Resin | Beige |
| Contact Position | Bottom |
| Durability (mating cycles max) | 25 |
| Entry Angle | 90° Angle |
| Mated Height | 1.90mm |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Gold over Nickel |
| Material - Plating Termination | Gold over Nickel |
| Material - Resin | Liquid Crystal Polymer |
| Net Weight | 126.330/mg |
| Number of Rows | 1 |
| Orientation | Right Angle |
| PCB Locator | No |
| PCB Retention | Yes |
| Packaging Type | Embossed Tape on Reel |
| Pitch - Mating Interface | 1.00mm |
| Pitch - Termination Interface | 1.00mm |
| Plating min - Mating | 0.051µm |
| Plating min - Termination | 0.051µm |
| Polarized to PCB | Yes |
| Stackable | No |
| Temperature Range - Operating | -40°C to +105°C |
| Termination Interface: Style | Surface Mount |
| Wire/Cable Type | FFC/FPC |

Electrical

| | |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum | 50V AC (RMS)/DC |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|--|
| Packaging Specification | 2005289200 |
| Product Specification | 2005280000 |
| Sales Drawing | 2005280000, 2005280006, 2005281000, 2005281006 |

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[200528](#) Series

This document was generated on 07/08/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION