

### General Information

|                        |  |
|------------------------|--|
| Extended Product Type: | OHYS2RJ  |
| Product ID:            | 1SCA105323R1001  |
| EAN:                   | 6417019412436  |
| Catalog Description:   | OHYS2RJ Handle   |
| Long Description:      | Selector type handle. Indication I-O and ON-OFF. No separate shaft needed. Padlockable with max. 3 padlocks, IP 65, hole distance 36/48 mm, NEMA 1, 3R, 12, red-yellow, OT16...125FT |

### Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

### Ordering

|                         |               |
|-------------------------|---------------|
| EAN:                    | 6417019412436 |
| Minimum Order Quantity: | 10 piece      |
| Customs Tariff Number:  | 85381000      |

### Dimensions

|                     |        |
|---------------------|--------|
| Product Net Width:  | 65 mm  |
| Product Net Height: | 65 mm  |
| Product Net Depth:  | 44 mm  |
| Product Net Weight: | 0.1 kg |

### Container Information

|                               |               |
|-------------------------------|---------------|
| Package Level 1 Units:        | 1 piece       |
| Package Level 1 Width:        | 65 mm         |
| Package Level 1 Height:       | 44 mm         |
| Package Level 1 Length:       | 65 mm         |
| Package Level 1 Gross Weight: | 0.1 kg        |
| Package Level 1 EAN:          | 6417019412436 |

### Environmental

|              |  |
|--------------|--|
| RoHS Status: | Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-07-01 |
|--------------|--|

### Additional Information

|                             |                               |
|-----------------------------|-------------------------------|
| Color:                      | Red-Yellow                    |
| Degree of Protection:       | IP65                          |
| Handle Type:                | Selector                      |
| IIT Publishing Status:      | Level 0 - Information enabled |
| Order Multiple:             | 10 piece                      |
| Product Main Type:          | OHYS2RJ                       |
| Product Name:               | Handle                        |
| Product Type:               | OHYS                          |
| Suitable For:               | OT16 ... 125FT                |
| Suitable for Product Class: | Switch disconnectors          |

### Certificates and Declarations (Document Number)

|                                    |                 |
|------------------------------------|-----------------|
| Data Sheet, Technical Information: | 1SCC301020C0201 |
| RoHS Information:                  | 1SCC390005D0202 |

### Classifications

|                             |   |
|-----------------------------|---|
| ETIM 5:                     | EC000229 - Handle for power circuit breaker |
| Object Classification Code: | N/A   |

