

General Information

| | |
|------------------------|--|
| Extended Product Type: | 216MHS6 |
| Product ID: | 2CMA167623R1000 |
| EAN: | 7392696676236 |
| Catalog Description: | Switched interlocked socket-outlet, 6h, 16A, IP44, 2P+E |
| Long Description: | Switched Interlocked Socket Outlet, horisontal, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Blue |

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Switched Interlocked Socket Outlets, Horisontal

Ordering

| | |
|-------------------------|---------------------|
| EAN: | 7392696676236 |
| Minimum Order Quantity: | 1 piece |
| Country of Origin: | Czech Republic (CZ) |

Dimensions

| | |
|---------------------|---------|
| Product Net Width: | 168 mm |
| Product Net Height: | 129 mm |
| Product Net Length: | 116 mm |
| Product Net Depth: | 129 mm |
| Product Net Weight: | 0.58 kg |

Container Information

| | |
|-------------------------------|---------------|
| Package Level 1 Width: | 144 mm |
| Package Level 1 Length: | 202 mm |
| Package Level 1 Height: | 140 mm |
| Package Level 1 Gross Weight: | 0.66 kg |
| Package Level 1 EAN: | 7392696676236 |
| Package Level 1 Units: | 1 piece |

Environmental

| | |
|--------------|---|
| RoHS Status: | Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1 |
|--------------|---|

Certificates and Declarations (Document Number)

| | |
|---------------------------------|-----------------|
| Declaration of Conformity - CE: | 2CMC700005D0001 |
| Environmental Information: | 2CMC700001D0002 |
| RoHS Information: | 2CMC700057D0001 |

Additional Information

| | |
|----------------------------------|--|
| Additional Information: | Cable entry, knock-outs Ø25mm/M25 |
| Cable Cross-Section: | 1.5 ... 4 mm ² |
| Cable Entry Position: | Top and bottom |
| Cable Outlets Per Side: | 1xØ25 |
| Color: | Blue |
| Degree of Protection: | acc. to IEC 60529 IP44 |
| Enclosure Material: | Thermoplastic |
| Frequency (f): | 50 Hz |
| Function: | Switched interlocked socket outlet, horisontal |
| IIT Publishing Status: | Level 0 - Information enabled |
| Invoice Description: | Ind. P&S#216MHS6 |
| Mounting Type: | Horisontal |
| Number of Poles: | 2 |
| Object Classification Code: | 2CMT005069 |
| Product Main Type: | CMHS |
| Product Name: | Industrial Switched Interlocked Socket Outlet |
| Protection Type: | Splashproof |
| Rated Current (I _n): | 16 A |
| Rated Voltage (U _r): | 200 ... 250 V |
| RoHS Date: | L23 |

| | |
|------------------------------------|---|
| Standards: | IEC 60 309-1, -2, -4 |
| Suitable For: | Switched Interlocked Socket Outlets, Horizontal |
| Suitable for Product Class: | Industrial Plugs and Sockets |

Classifications

| | |
|------------------|----------|
| E-number: | 2416812 |
| UNSPSC: | 39120000 |

