

POWER FISHING SYSTEMS

690-15 · 390 · 591 · 592



**WORKS HARDER.
LASTS LONGER.**

USA PHONE 800.435.0786
FAX 800.451.2632

CANADA PHONE 866.384.8813
FAX 800.524.2853

INT'L PHONE +1.815.397.7070
FAX +1.815.397.9247



GREENLEE®
A Textron Company

POWER VAC 690-15



PERFORMANCE.

- Industrial strength two-stage motor for long runs and extended life.

DURABILITY.

- Toughened 1/4" thick walls
- Washable stainless steel filter

MOBILITY.

- Rugged 8" wheels with dual front casters.
- 15' hose for maximum versatility on the jobsite.

Long 15' hose
for higher and harder
to reach locations.

**Steel transport
handle and rugged
8" wheels**
for easy
movement
around the
jobsite.

**Large, durable
outer tank.**
Impact resistant
for long life.



Industrial two-stage motor
for consistent pressure over long runs.

Washable, stainless steel filter
for easy cleaning – no need
to replace filter.



SPECIFICATIONS

Voltage	120VAC
Peak Amperage	11.8A
Motor Type	Two-Stage Bypass
Impellor Size (In.)	7.2
Max Vacuum (In. of Water)	112.8
Max Blower (PSI)	4.0
Max Airflow (CFM)	107.0
Tank Capacity (US Gallons)	12
Shipping Weight (lbs.)	58.6

Designed and assembled in the USA.

A FULL LINE OF POWER FISHING FROM GREENLEE



690-RM

REPLACEMENT MOTOR FOR 690-15

- Full replacement motor unit with stainless steel filter.
- Fits 690-15 and previous models*



690-RT

REPLACEMENT TANK FOR 690-15

- Full replacement tank unit.
- Fits 690-15 and previous models*



REPLACEMENT HOSES

- Available in sizes:
 - » 10' x 1½" **(RH10)**
 - » 15' x 1½" **(RH15)**
 - » 25' x 1½" **(RH25)**



392

ACCESSORY KIT

- Includes: Fish line – 85lbs. Pulling strength, 2,150' long; Pistons for ½" – 2" conduit, ½" – 2¼" Cone adapters, adapter nozzle for measuring tape, accessory container and lid



24779
Replacement Kit for 690

CONDUIT PISTONS

- Pistons available in ½" – 6"
- for all conduit types
- Color-coded for easy identification



390

LI'L FISHER® POWER FISHING SYSTEM

- Compact high performance unit for blowing and vacuuming. Includes: 390 Vac unit and 10' hose. See model 392 for power fishing accessories.



591

PORTABLE BLOWER POWER FISHING SYSTEM

- Portable for remote blowing applications.
- Includes: Mighty Mouser® Blow Gun, Fish Line – 85lbs. pulling strength; 2,150' long, 1' x 1½" and 4' x 1½" Flexible Hose, Hose Clamp, Pistons for ½" – 4" conduit, adapter nozzle for measuring tape and line, storage box and lid, 1¼" – 4" Cone adapters



592

MIGHTY MOUSE® BLOW GUN KIT

- Full accessory kit for dispensing pulling line.
- Includes: Mighty Mouser® Blow Gun, Fish line – 85lbs. Pulling strength; 2,150' long, 1' x 1½" Flexible Hose, Pistons for ½" – 4" conduit, storage box and lid, 1¼" – 1" Cone adapters, Hose Clamp

FOR PRODUCT VIDEOS, DEMONSTRATIONS
AND MORE, SCAN THIS QR CODE OR VISIT:



www.youtube.com/GreenleeDEMO



POLY LINE AND MEASURING/ PULLING TAPE*



435



430



4436

Greenlee offers a complete range of poly line and measuring tape for all kinds of cable pulls.

- Poly Line: Ready to use, pre-punched hole in lid with resealable cap.
- Tape: 3-in-1 usage for fishing, measuring, and light pulling.
- Long shelf life: All lines and tape are rot and mildew resistant.

*Sold separately

ORDERING INFORMATION

CAT NO.	DESCRIPTION
690-15	690 Power Fishing System - 15' Hose
690-RM	Replacement Motor Kit for 690
690-RT	Replacement Tank Kit for 690
RH10	10' x 1½" Vacuum/blower Hose
RH15	15' x 1½" Vacuum/blower Hose
RH25	25' x 1½" Vacuum/blower Hose
390	390 Li'l Fisher™ Power Fishing Unit
591	591 Might Mouser™ Portable Blower Fishing System
592	Mighty Mouser™ Blow Gun Kit
392	Power Fishing Accessory Kit

CAT NO.	DESCRIPTION
430	Poly Line Bucket – 6,500ft, 210lb (Green Tracer)
430-500	Poly Line Dispenser – 500ft, 210lb (Green Tracer)
431	Poly Line Bucket – 5,200ft, 240lb (Yellow Tracer)
37959	Poly Line Bucket – 2,200ft, 500lb (Red Tracer)
435	Conduit Measuring Tape – 3/16" x 3,000ft, 170lb
4435	Polyester Pull/Measure Tape – ½" x 3,000ft, 1,250lb
4436	Polyester Pull/Measure Tape – 5/8" x 3,000ft, 1,800lb
4437	Polyester Pull/Measure Tape – ¾" x 3,000ft, 2,500lb
24779	½" – 4" Piston Set for All Conduit
S2613	½" – 2" Piston Set for All Conduit
34317	2½" – 4" Piston Set for EMT Conduit



www.greenlee.com MA-5986 07/13

4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070

©2013 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA

Greenlee Textron Inc. is a subsidiary of Textron Inc.

