

## E-SERIES ULTRAVIOLET HAND-HELD LAMPS

Product Number	Ultraviolet Wavelength (nm)	Equipped With	Housing Dimensions W x L x H	Replacement Tubes	Replacement Filter
EA-140	365	One 4-Watt Integrally Filtered BLB Tube	3.25" x 7" x 2.5" (8.3cm x 17.8cm x 6.4cm)	BLE-220B	--
EN-140	365	One 4-Watt Tube	3.25" x 7" x 2.5" (8.3cm x 17.8cm x 6.4cm)	BLE-270W	--
EN-140L	365	One 4 Watt Tube with Filter Assembly	3.25" x 8" x 2.5" (8.3cm x 20.3cm x 6.4cm)	BLE-270W	2F003
EA-240	365	Two 4-Watt Integrally Filtered BLB Tubes	3.25" x 7" x 2.5" (8.3cm x 17.8cm x 6.4cm)	BLE-220B	--
EA-150	365	One 5-Watt Integrally Filtered BLB Tube	3.25" x 8" x 2.5" (8.3cm x 20.3cm x 6.4cm)	BLE-50H	--
EA-160	365	One 6-Watt Integrally Filtered BLB Tube	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-480B	--
EN-160	365	One 6-Watt Tube	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6T365	--
EN-160L	365	One 6-Watt Tube with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6T365	2F005
EA-180	365	One 8-Watt Integrally Filtered BLB Tube	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-760B	--
EN-180	365	One 8-Watt Tube	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T365	--
EN-180L	365	One 8 Watt Tube with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T365	2F082
EN-280L	365	Two 8-Watt Tubes with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T365	2F082
EB-160C	312	One 6-Watt Tube with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6T312	2F006
EB-180C	312	One 8-Watt Tube with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T312	2F018
EB-280C	312	Two 8 Watt Tubes with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T312	2F018
EF-140C	254	One 4-Watt Tube with Filter Assembly	3.25" x 8" x 2.5" (8.3cm x 20.3cm x 6.4cm)	BLE-2537S	2F001
EF-160C	254	One 6-Watt Tube with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6254S	2F006
EF-180C	254	One 8-Watt Tube with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T254	2F018
EF-260C	254	Two 6-Watt Tubes with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6254S	2F006
EF-280C	254	Two 8-Watt Tubes with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T254	2F018
ENF-240C	365/254	One 4-Watt Tube Each Wavelength with Filter Assembly	3.25" x 8" x 2.5" (8.3cm x 20.3cm x 6.4cm)	BLE-270W BLE-2537S	2F001
ENF-260C	365/254	One 6-Watt Tube Each Wavelength with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6T365 BLE-6254S	2F006
ENF-280C	365/254	One 8-Watt Tube Each Wavelength with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T365 BLE-8T254	2F018
ENB-260C	365/312	One 6-Watt Tube Each Wavelength with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6T365 BLE-6T312	2F006
ENB-280C	365/312	One 8-Watt Tube Each Wavelength with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T365 BLE-8T312	2F018
EBF-260C	312/254	One 6-Watt Tube Each Wavelength with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6T312 BLE-6254S	2F006
EBF-280C	312/254	One 8-Watt Tube Each Wavelength with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T312 BLE-8T254	2F018
EF-140	254	One 4-Watt Tube, Germicidal	3.25" x 7" x 2.5" (8.3cm x 17.8cm x 6.4cm)	BLE-2537S	--
EF-160	254	One 6-Watt Tube, Germicidal	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6254S	--
EF-180	254	One 8-Watt Tube, Germicidal	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T254	--

## E/12-SERIES 12-VOLT RECHARGEABLE BATTERY OPERATED UV LAMPS

Product Number	Ultraviolet Wavelength (nm)	Equipped With	Housing Dimensions W x L x H	Replacement Tubes	Replacement Filter
EA-140/12	365	One 4-Watt Integrally Filtered BLB Tube	3.25" x 7" x 2.5" (8.3cm x 17.8cm x 6.4cm)	BLE-220B	--
EN-140/12	365	One 4-Watt Tube	3.25" x 7" x 2.5" (8.3cm x 17.8cm x 6.4cm)	BLE-270W	--
EN-140L/12	365	One 4 Watt Tube with Filter Assembly	3.25" x 8" x 2.5" (8.3cm x 20.3cm x 6.4cm)	BLE-270W	2F003
EA-240/12	365	Two 4-Watt Integrally Filtered BLB Tubes	3.25" x 7" x 2.5" (8.3cm x 17.8cm x 6.4cm)	BLE-220B	--
EA-150/12	365	One 5-Watt Integrally Filtered BLB Tube	3.25" x 8" x 2.5" (8.3cm x 20.3cm x 6.4cm)	BLE-50H	--
EA-160/12	365	One 6-Watt Integrally Filtered BLB Tube	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-480B	--
EN-160/12	365	One 6-Watt Tube	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6T365	--
EN-160L/12	365	One 6-Watt Tube with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6T365	2F005
EA-180/12	365	One 8-Watt Integrally Filtered BLB Tube	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-760B	--
EN-180/12	365	One 8-Watt Tube	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T365	--
EN-180L/12	365	One 8 Watt Tube with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T365	2F082
EN-280L/12	365	Two 8-Watt Tubes with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T365	2F082
EB-160C/12	312	One 6-Watt Tube with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6T312	2F006
EB-180C/12	312	One 8-Watt Tube with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T312	2F018
EB-280C/12	312	Two 8 Watt Tubes with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T312	2F018
EF-140C/12	254	One 4-Watt Tube with Filter Assembly	3.25" x 8" x 2.5" (8.3cm x 20.3cm x 6.4cm)	BLE-2537S	2F001
EF-160C/12	254	One 6-Watt Tube with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6254S	2F006
EF-180C/12	254	One 8-Watt Tube with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T254	2F018
EF-260C/12	254	Two 6-Watt Tubes with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6254S	2F006
EF-280C/12	254	Two 8-Watt Tubes with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T254	2F018
ENF-240C/12	365/254	One 4-Watt Tube Each Wavelength with Filter Assembly	3.25" x 8" x 2.5" (8.3cm x 20.3cm x 6.4cm)	BLE-270W BLE-2537S	2F001
ENF-260C/12	365/254	One 6-Watt Tube Each Wavelength with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6T365 BLE-6254S	2F006
ENF-280C/12	365/254	One 8-Watt Tube Each Wavelength with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T365 BLE-8T254	2F018
ENB-260C/12	365/312	One 6-Watt Tube Each Wavelength with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6T365 BLE-6T312	2F006
ENB-280C/12	365/312	One 8-Watt Tube Each Wavelength with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T365 BLE-8T312	2F018
EBF-260C/12	312/254	One 6-Watt Tube Each Wavelength with Filter Assembly	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6T312 BLE-6254S	2F006
EBF-280C/12	312/254	One 8-Watt Tube Each Wavelength with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T312 BLE-8T254	2F018
EF-140/12	254	One 4-Watt Tube, Germicidal	3.25" x 7" x 2.5" (8.3cm x 17.8cm x 6.4cm)	BLE-2537S	--
EF-160/12	254	One 6-Watt Tube, Germicidal	3.25" x 10.25" x 2.5" (8.3cm x 26.0cm x 6.4cm)	BLE-6254S	--
EF-180/12	254	One 8-Watt Tube, Germicidal	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-8T254	--

## B-SERIES BATTERY OPERATED UV LAMPS

Product Number	Ultraviolet Wavelength (nm)	Equipped With	Housing Dimensions W x L x H	Replacement Tubes	Replacement Filter
B-14N	365	One 4-Watt Integrally Filtered BLB Tube	3.25" x 8" x 2.5" (8.3cm x 20.3cm x 6.4cm)	BLE-220B	--
B-14F	254	One 4-Watt Tube with Filter Assembly	3.25" x 8" x 2.5" (8.3cm x 20.3cm x 6.4cm)	BLE-2537S	2F001
B-160	365	Rechargeable Lantern, 6V with AC Recharger	3.25" x 5.75" x 10" (8.3cm x 14.6cm x 25.4cm)	BLE-480B	--
BEA-140	365	One 4-Watt Tube Integrally Filtered BLB Tube	3.25" x 8" x 2.5" (8.3cm x 20.3cm x 6.4cm)	BLE-220B	--
BEF-140C	254	One 4-Watt Tube with Filter Assembly	3.25" x 8" x 2.5" (8.3cm x 20.3cm x 6.4cm)	BLE-2537S	2F001
BEA-160	365	One 6-Watt Integrally Filtered BLB Tube	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-480B	--
BEB-160C	312	One 6-Watt Tube with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-6T312	2F018
BEF-160C	254	One 6-Watt Tube with Filter Assembly	3.25" x 13.25" x 2.5" (8.3cm x 33.7cm x 6.4cm)	BLE-6254S	2F018