Fine screwdriver set PicoFinish electric





Simplifies your work: Sensitive working due to slim handle and rotating cap. Increases your efficiency: Screwdriver handle size concept for an optimal balance between precision and control. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Slotted, Phillips 6-pcs.				
Order-No.		_		
38996		1		
Θ	1,5 x 40 / 2,0 x 40 / 2,5 x 60 / 3,0 x 60			
⊕	PH00 x 40 / PH0 x 60			
DINI ISO 976	Manufactured acc. to IEC 60000:2012			

Fine screwdriver PicoFinish electric





Simplifies your work: Sensitive working due to slim handle and rotating cap. Increases your efficiency: Screwdriver handle size concept for an optimal balance between precision and control. Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

⊖Slotted 2:					
Order-No.	\ominus	⇌	\ominus ;		–
38874	1,5	40	0,25	18	10
38875	2,0	40	0,4	18	10
38876	2,5	60	0,4	18	10
38877	3,0	60	0,5	18	10
38878	3,5	60	0,6	18	10
Manufactured acc. to IEC 60900:2012.					

⊕ Phillips 22				
Order-No.	①	=	— <u></u>	_
38879	PH00	40	18	10
38880	PH0	60	18	10
38881	PH1	60	18	10
Manufactured acc. to IEC 60900:2012.				

INFOBOX:

PicoFinish electric



Wiha PicoFinish electric: The VDE-GS tested precision screwdriver.

- The smooth-running turn-cap enables fast turning.
- Imprint with the screw symbol and sizes eases recognition.

Ratchet with pistol handle Topra 2K electric

Voltage tester Volt Detector non-contact, single-pole, 230-1,000 V AC





Simplifies your work: Voltage tester operational at all times through automatic activation. **Increases your efficiency:** Fast voltage testing thanks to non-contact measurement within a field of 4mm.

	255-12
Order-No.	
37871	10
IEC 61010-1	



Simplifies your work: Unique Topra handle combines the advantages of a long handle and T-handle. **Saves time:** Single-hand operation of the ratchet permits easy and fast fastening without having to re-position the tool. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

0		282700
Order-No.	0	
39069	6,0	1

Voltage tester SoftFinish® single-pole, 110-250 volts





Increases your efficiency: Stable and as robust as a fully-fledged screwdriver. **Offers you full protection:** Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Θ					255-11
Order-No.	\ominus	=	\ominus ;	- →	
34745	3,0	60	0,5	19	10
Tested according to DIN 57680-6, GS, CE compliant.					

Screwdriver set SoftFinish®





Protects your health: With the patented SoftFinish® handle design, ensuring work is kind to hands and muscles. Recommended by doctors and therapists at German Campaign for Healthier Backs. **Increases your efficiency:** The unique Wiha handle size concept with optimal balance between power and control.

assorted 12-pcs.

4,0 x 100 / 3,5 x 100 /

PZ1 x 80 / PZ2 x 100

PH1 x 80 / PH2 x 100 / PH3 x 150

T15 x 80 / T20 x 100 / T25 x 100 / T30 x 115

6,5 x 150

Order-No. 41002

 \oplus

₩

302 HK12



- The convenient expert for dry applications.
- The SoftFinish handle provides optimal grip for dry applications in trade and industry.
- The position of the soft and hard zones on the handle also supports the perfect grip for quick and powerful turning.