

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015445816](#)
Status: **Active**
Overview: C-Grid® Products
Description: 2.54mm Pitch C-Grid® Receptacle, Through Hole, Dual Row, High Profile, Vertical, High-Temperature, 16 Circuits

Documents:

[3D Model](#) [Product Specification PS-70181-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family PCB Receptacles
Series [71850](#)
Application Board-to-Board, Signal
Overview [C-Grid® Products](#)
Product Name C-Grid®
UPC 800754248747

Physical

Circuits (Loaded) 16
Circuits (maximum) 16
Color - Resin Black
Durability (mating cycles max) 50
Flammability 94V-0
Glow-Wire Compliant No
Material - Metal Phosphor Bronze
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 1.337/g
Number of Rows 2
Orientation Vertical
PC Tail Length 3.05mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.57mm
Packaging Type Tray
Pitch - Mating Interface 2.54mm
Plating min - Mating 0.381µm
Plating min - Termination 1.905µm
Polarized to PCB No
Temperature Range - Operating -40°C to +105°C
Termination Interface: Style Through Hole

Electrical


Current - Maximum per Contact 2.5A
Voltage - Maximum 250V

Solder Process Data

Lead-freeProcess Capability SMC&WAVE
Process Temperature max. C 260

Material Info

Engineering Number A718500135



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[71850](#) Series

Mates With

[8624](#) , [70203](#) , [70246](#) Straight Header,
[70247](#) Right Angle Header, [70287](#) , [70289](#)
 , [70227](#) , [70567](#) , [70280](#) , [70524](#) , [70260](#) ,
[8723](#) , [70568](#) , [8724](#) , [71764](#) , [70229](#) , [70](#)
[216](#) , [71308](#)

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-70181-001
SDA-71850-0***

This document was generated on 05/23/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION