

DIN rail bus connectors - HBUS 53,6-16P-3S BK - 2896322

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plug component, Nominal current: 3 A, Number of positions: 16, Pitch: 2.54 mm, Color: jet black

Why buy this product



Key Commercial Data

Packing unit	10 STK
GTIN	 4 046356 096775
GTIN	4046356096775
Weight per Piece (excluding packing)	18.170 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701

DIN rail bus connectors - HBUS 53,6-16P-3S BK - 2896322

Classifications

eCl@ss

eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440309
eCl@ss 9.0	27440309

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002638
ETIM 6.0	EC002638

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 118976
Nominal current I _N	2 A		
Nominal voltage U _N	30 V		

DIN rail bus connectors - HBUS 53,6-16P-3S BK - 2896322

Approvals

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 118976
Nominal current I _N		2 A	
Nominal voltage U _N		30 V	

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm
------------------	---	---

Accessories

Accessories

Filler plug

Printed-circuit board connector - HBUS-B SET BK - 2278173



Set of 3 caps, for protecting unused DIN rail bus connectors, simply snap on to fit

Electronic housing - BSL-2,54/16-ST 40CM - 2202938



Cable bridge for cross-DIN-rail connection of the HBUS connector

Electronic housing - BSL2-2,54/16-ST - 2201281



Cable bridge for cross-DIN-rail connection of the HBUS connector

DIN rail bus connectors - HBUS 53,6-16P-3S BK - 2896322

Accessories

Power plug - SL2-2,54/16-ST - 2896348



Power connector for DIN rail bus connector with 16 free cable ends with a cross section of 0.25 mm², 500 mm long, male contacts

Power plug - BL2-2,54/16-ST - 2896335



Power connector for DIN rail bus connector with 16 free cable ends with a cross section of 0.25 mm², 500 mm long, female contacts

Necessary add-on products

Pin strip - PSTD 0,65X0,65/9-H-2,54 - 2200701



Pin strip (horizontal)