

Capsule-Type Surface-Mount Contacts

SM-4004-TQ/W

1" Gap, N.C., Quick-Connect, White

SM-4004-LQ/W

¾" Gap, N.C., 18" Wire Leads, White

Features:

- Miniature capsule-type surface-mount magnetic contacts
- Gold-plated external screw terminals for longer life and reliability with tape to cover terminals (SM-4004-TQ only)
- 18" Wire leads (SM-4004-LQ only)
- Adhesive mounting (double sided tape included)
- Contact reed switch is SPST, iridium-plated to have a high melting point and Vickers hardness, which results in higher handling power and long life (SM-4004-TQ), or ruthenium on gold under plating, which results in a long life (SM-4004-LQ)
- 1" (25mm) Gap (SM-4004-TQ)
- ¾" (19mm) Gap (SM-4004-LQ)
- For N.C. circuits
- Lifetime limited warranty



SM-4004-TQ/W



SM-4004-LQ/W



Long-Life Contacts

Rare-Earth Magnet


18" Leads or Quick-Connect

Miniature Capsule-Type

Specifications:

| Model number | SM-4004-TQ/W | SM-4004-LQ/W |
|-------------------|---------------------------|--------------------------------|
| Circuit type | N.C. | |
| Operation Gap | 1" (25mm) | ¾" (19mm) |
| Terminals | Gold-plated quick-connect | 18" wire leads |
| Color | White | |
| Material | High-impact ABS plastic | |
| Contacts | Iridium plating | Ruthenium on gold underplating |
| Contact rating | 0.1A@100VDC (max) | |
| | 1.0A@10VDC (max) | |
| | 10W (max) | |
| Temperature | -68°~158°F (-20°~70°C) | |
| Switch cycles | 50 Million (0.1mA@5VDC) | |
| Switch dimensions | 1"x3/8"x1/4" (25x10x7mm) | |
| Magnet dimensions | 1"x3/8"x1/4" (25x10x7mm) | |
| Magnet type | Rare-earth neodymium | |

Dimensions:



SECO-LARM® U.S.A., Inc.

16842 Millikan Avenue, Irvine, CA 92606

Phone: (949) 261-2999 | (800) 662-0800 Fax: (949) 261-7326

Website: www.seco-larm.com Email: sales@seco-larm.com



Copyright 2015 © SECO-LARM U.S.A., Inc. All rights reserved. All trademarks are the property of SECO-LARM U.S.A., Inc. or their respective owners. The SECO-LARM policy is one of continual development. For that reason, SECO-LARM reserves the right to change prices and specifications without notice. SECO-LARM is not responsible for misprints.

SECO-LARM® ENFORCER® CRIMEBUSTER® CBA SLI®

PiSM-4004-TQ_150320.docx