

UltimaPro X2 microSDHC/XC V90 UHS-II Card

CLASS 10

READ 280MB/s*
WRITE 240MB/s*



V90

Suitable for



High Endurance pSLC

32 GB

64 GB

INTRODUCTION

UltimaPro X2 microSDHC/XC are professional grade memory cards from Integral featuring the UHS-II interface and designed to complement the latest action cameras, drones, pro-grade cameras, smartphones and tablets. Our advanced chip-set delivers blistering read and write speeds up to 280MB/s and 240MB/s. Ideal for recording 8K, 4K, 2K, Full HD, 3D video and RAW and JPEG images.

FEATURES

- Large RAW and JPEG images can be saved to UltimaPro X2 memory cards at ultra-fast speed, with no lag-great for burst-mode photography.
- Certified to V90 (Video 90) standard. V90 SDHC/XC memory cards offer 90MB/s sustained video recording with no dropped frames.
- Designed to support cinema-grade video recording, ensuring smooth video capture at up to 8K resolution (7680x4320). Ideal for today's 4K UHD and Full HD devices and future-proof for 8K video.
- Made from Pseudo SLC (pSLC). Compared to normal MLC (used in other high-performance cards), Integral UltimaPro X2 memory delivers 6 times more endurance. Providing a substantial 20,000 Read/Write cycles, Integral UltimaPro X2 memory cards are ideal for use by photography and video professionals and in industrial applications such as video security recording.
- Optimised for high-performance devices that support UHS-II (Ultra-High-Speed Interface 2)
- Backwards compatible with UHS-I host devices, with a performance up to UHS-I speed that host device will allow.

- Store more apps, images, music, games, and video on your tablet PC and smartphone than ever before
- UHS-II SD Adapter included
- 5 year warranty

*Up to 280MB/s read speed and up to 240MB/s write speed. Based on internal testing; performance may vary depending on host device. UHS-II host required for full performance.

PRODUCT TYPE

microSDHC/XC Card

INTERFACE TYPE

16 Pin UHS-II

ENVIRONMENTAL PARAMETERS

Min Operating Temperature 0°C

Max Operating Temperature 70°C

COMPLIANT STANDARD

Secure Digital Association

	HEIGHT	WIDTH	DEPTH	WEIGHT
PRODUCT	11mm	15mm	1mm	0.5g
PACKED	138mm	93mm	8mm	19g

CAPACITY	PART CODE	BARCODE (EAN)
32GB	INMSDH32G-280/240U2	5055288436132
64GB	INMSDX64G-280/240U2	5055288436169

Product design and specification subject to change or modification without notice. E&OE.

All trademarks acknowledged.

For warranty information please visit www.integralmemory.com/warranty