

4-Channel RF Transmitters & Receiver

SK-919T4J – Four-Button Fixed-Code RF Transmitter SK-917T4J – Four-Button CODEBUMP™ Transmitter

- ▶ Operates up to 500 feet. 315 MHz.
- ▶ LED transmission indicator.
- ▶ Attractive slim-line design.
- ▶ Includes 12VDC alkaline battery.
- ▶ Compatible with all SECO-LARM receivers.

2" x 1 1/2" x 19/32"
(50 x 38 x 15 mm)



SK-910R4 – Four-Channel Receiver (11 to 24 VAC/DC)

- ▶ Control garage doors, gates, house lights, alarm panels, or other devices via remote.
- ▶ Compatible with all SECO-LARM transmitters (fixed code and CODEBUMP™).
- ▶ 4 LEDs, one per channel, indicate RF reception, learn mode, transmitter learned, memory cleared, output type.
- ▶ Four Form "C" dry relay outputs (N.O./N.C./Com), max. 10Amp @ 24VDC.
- ▶ Programmable independent outputs: timed, momentary (1,2,3,4,5,10,30,60 sec.) toggle (ON/OFF), latched, validity.

4 3/8" x 5 5/16" x 1 1/8"
(111 x 135 x 28 mm)



*Increase range with SECO-LARM's
Extended Range Antenna (SK-91ERSD).*

SK-919TP4H-NU

Four-Button Handheld Transmitter

- ▶ Operates up to 500 feet.
- ▶ Over 68 billion (6.8 x 10¹⁰) possible codes.
- ▶ Includes two 3VDC lithium batteries.
- ▶ Visor clip and belt clip included. Belt clip holster & wall mount bracket also available (Model: SK-9HBC).
- ▶ Slim-line design.



3 1/2" x 2 3/16" x 1/2"
(89 x 56 x 12 mm)

Technical Specifications:

	SK-910R4
Operating Distance	Up to 500 feet open air
Operating Temperature	-4°~162° F (-20°~72° C)
Current Drain	8mA at 12VDC (standby), 45mA at 12VDC (LED flashing)
Sensitivity	-87dBm (typical)
Data Format	PWM
RF Codes	68 billion
Coded Channels	Four
Stored Transmitter Codes	15 per channel
Receiver Outputs	Form "C" dry relay contact (N.O./N.C./Com; max. 10 Amp @ 24VDC)
Receiver Output Modes	Programmable 1,2,3,4,5,10,30,60 sec. momentary (default), toggle, or validity

Copyright 2009 SECO-LARM U.S.A., Inc. Allrights reserved.

The SECO-LARM policy is one of continual development. For that reason, SECO-LARM reserves the right to change prices and specifications without notice. SECO-LARM is not responsible for misprints.

SECO-LARM[®]

16842 Millikan Avenue, Irvine, CA 92606

1.949.261.2999 (CA & Int'l)
Email: info@seco-larm.com

1.800.662.0800 Fax: 1.949.261.7326
Website: www.seco-larm.com



RF4Ch012109.cdr