

# Remote Control Module for Tripp Lite Pure Sine-Wave Inverter/Chargers

MODEL NUMBER: APSRMSW



### **Highlights**

- LEDs indicate battery and power status at a glance
- On/off button for instant one-touch control
- Suited for front-panel, rear-panel or below-dash mounting
- · Molded plastic housing
- Attractive faceplate for front-panel installation

#### **Package Includes**

- APSRMSW Remote Control Module
- Faceplate
- Remote control cord, 32 ft.
- Mounting hardware
- Owner's manual

#### Description

The APSRMSW Remote Control Module lets you monitor and control your Tripp Lite APS1012SW, APS2012SW, APSX1012SW or APSX2012SW sine-wave inverter/charger from up to 32 feet away. Ideal for automotive, remote site, industrial, commercial and residential applications, the APSRMSW mounts easily on a fixed, flat surface, so you can control your inverter/charger from the comfort of your vehicle.

Monitor battery status, charger status and power conditions at a glance via the front-panel LEDs. The molded plastic housing also includes an on/off button that gives you instant one-touch control of the connected inverter/charger. Built-in mounting slots and a 32-foot cable provide plenty of flexibility in mounting and operating the APSRMSW. A faceplate is included for front-panel mounting in an RV, boat or other vehicle.

#### **Features**

#### Control Your Inverter/Charger Up to 32 Ft. Away

- Ideal for automotive, remote site, industrial, commercial and residential applications
- Allows complete remote monitoring and control of Tripp Lite APS1012SW, APS2012SW, APSX1012SW and APSX2012SW sine-wave inverter/chargers

#### **Intuitive Front Panel Indicators**

- LEDs show battery status, charger status and power conditions at a glance
- On/off button for one-touch control of connected inverter/charger

#### **Built-In Mounting Slots**

- Installs in variety of locations and configurations, including front-panel, rear-panel and below-dashboard
- Molded plastic housing
- Faceplate included for front-panel mounting

## **Specifications**





OVERVIEW	
Accessories Type	Remote Control Module
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LEDs	Battery Charge and Operational LEDs
Switches	Remote Control Switch
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.71 x .4.41 x 6.61
Shipping Dimensions (hwd / cm)	6.88 x 11.20 x 16.79
Shipping Weight (lbs.)	.44
Shipping Weight (kg)	.20
Unit Dimensions (hwd / in.)	3.86 x 1.89 x .85
Unit Dimensions (hwd / cm)	9.80 x 4.80 x 6.61
Unit Weight (lbs.)	1.0
Unit Weight (kg)	.45
Material of Construction	Molded Plastic
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies