

External 72V 2U Rackmount Battery Pack for select Tripp Lite UPS Systems (BP72V15-2U)

MODEL NUMBER: **BP72V15-2U**



Highlights

- Extends the runtime of compatible 72V Tripp Lite UPS Systems
- Supports 2U rackmount installation, 4 post installation accessories included
- Options for 2 post rackmount and wallmount installation available

Package Includes

- BP72V15-2U external battery pack with attached DC cabling
- 4 post compatible rack mounting hardware
- Owner's manual

Description

BP72V15-2U rackmount external battery pack offers extended battery runtime when used in conjunction with expandable 72V Tripp Lite rackmount and tower UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included mounting accessories support 2U rackmount installation in 4 post racks. Options for 2 post center-mounting and wall mount installation available.

Compatible with these UPS Systems - SMART3000RMOD2U, [SU3000RTXL2U](#), [SU3000RTXL3U](#), [SU3000RTXLCD2U](#), [SU3000RTXLCD3U](#), [SU3000RTXR3U](#), [SU3000RTXR3UHW](#), [SU3000XL](#), [SU3000XLCD](#), [SUIINT3000RTXL2U](#), [SUIINT3000RTXL3U](#), [SU3000LCD2UHV](#), [SUIINT3000LCD2U](#) and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 72V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Included mounting brackets support rackmount installation in 4 post racks using only 2 rack spaces (2U)
- [2POSTRMKITWM](#) option supports balanced 2 point center-mounting in 2 post equipment racks
- [2POSTRMKITWM](#) option also enables wallmount installation
- NOTE: LIMIT OF 1 BP72V15-2U PER UPS, SEE [BP72V18-2US](#) or [BP72V28RT-3U](#) FOR MULTI-PACK COMPATIBILITY

Specifications

BATTERY	
DC System Voltage (VDC)	72
UPS Connection	DC connector
Typical Battery Lifespan	4-6 years typical (North America)



PHYSICAL	
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount(2POSTRMKITWM); Wallmount(2POSTRMKITWM)
Minimum Required Rack Depth (inches)	31.75
Minimum Required Rack Depth (cm)	80.64
Shipping Dimensions (hwd / in.)	10 x 28.5 x 26.5
Shipping Dimensions (hwd / cm)	25.4 x 72.4 x 67.3
Shipping Weight (lbs.)	120
Shipping Weight (kg)	54.5
Unit Dimensions (hwd / in.)	3.5 x 17.5 x 20.75
Unit Dimensions (hwd / cm)	8.9 x 52.7 x 52.7
Unit Weight (lbs.)	72.4
Unit Weight (kg)	32.84
Material of Construction	Steel
External Battery Pack Form Factor	Rack
Minimum Required Rack Depth (mm)	806
WARRANTY	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>