

Fuse Kit Surface Mount Fuse UMT-H



**Description**

- Fuse Kit for quick sampling of customers and engineering design support
- More technical data and approvals see the specific datasheets

**References**

Fuse Kit to [UMT-H](#)

**Weblinks**

[pdf datasheet](#), [html-datasheet](#), [General Product Information](#), [Packaging details](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

**Fuse Kit UMT-H**

Type	Rated current	Rated Voltage [VAC]	Rated Voltage [VDC]	Amount	Part Number
UMT-H	160 mA	277	250	10 pieces	<a href="#">3403.0266.11</a>
UMT-H	200 mA	277	250	10 pieces	<a href="#">3403.0267.11</a>
UMT-H	250 mA	277	250	10 pieces	<a href="#">3403.0268.11</a>
UMT-H	315 mA	277	250	10 pieces	<a href="#">3403.0269.11</a>
UMT-H	400 mA	277	250	10 pieces	<a href="#">3403.0270.11</a>
UMT-H	500 mA	277	250	10 pieces	<a href="#">3403.0271.11</a>
UMT-H	630 mA	277	250	10 pieces	<a href="#">3403.0272.11</a>
UMT-H	1 A	277	250	10 pieces	<a href="#">3403.0274.11</a>
UMT-H	1.25 A	277	250	10 pieces	<a href="#">3403.0275.11</a>
UMT-H	1.6 A	277	250	10 pieces	<a href="#">3403.0276.11</a>
UMT-H	2 A	277	250	10 pieces	<a href="#">3403.0277.11</a>
UMT-H	2.5 A	277	125	10 pieces	<a href="#">3403.0278.11</a>
UMT-H	3.15 A	277	125	10 pieces	<a href="#">3403.0279.11</a>
UMT-H	4 A	277	125	10 pieces	<a href="#">3403.0280.11</a>
UMT-H	5 A	277	125	10 pieces	<a href="#">3403.0281.11</a>
UMT-H	6.3 A	277	125	10 pieces	<a href="#">3403.0282.11</a>
UMT-H	8 A	250	125	10 pieces	<a href="#">3403.0283.11</a>
UMT-H	10 A	250	125	10 pieces	<a href="#">3403.0284.11</a>

**Variants kit**

Description	Order Number
Fuse Kit UMT-H	<a href="#">3403.0299</a>

**Packaging Unit** 1 Pcs