

### Overview:

The HDMI 1x2 Splitter, 4K60 (500425) allows one (1) HDMI 2.0 source to be distributed to up to two (2) HDMI displays. The splitter supports up to 4K (3840 X 2160) video @ 60Hz, HDR, Deep Color and HD audio. The splitter is HDCP 1.4 & 2.2 compliant and features LED diagnostics. Additionally, all connectors are on the rear panel for neater cabling.



### Applications:


- Commercial and residential AV systems
- Classroom training systems
- Digital signage
- Boardroom systems
- Collaborative PC systems
- Medical information systems

### Key Features:

- Distribute one HDMI 2.0 source to two displays
- Supports up to 4K @ 60Hz (4:4:4)
- HDCP 1.4 and 2.2 compliant
- Supports HDR and Deep Color
- Supports LPCM 7.1CH, Dolby TrueHD, Dolby Atmos, DTS-HD Master Audio and DTS:X
- 16 position rotary switch for EDID management
- LED diagnostic
- Connectors on rear for neater cabling

<b>Environment</b>	HDMI 2.0a
<b>Devices</b>	Ultra HD Blu-Ray, projectors, monitors, TV, PC, laptops.
<b>Transmission</b>	Transparent to the user.
<b>Video Bandwidth</b>	18 Gbps
<b>Frequency Range</b>	25 to 600 MHz
<b>Signals</b>	HDMI 2.0a protocol.
<b>HDCP</b>	Revision 1.4 & 2.2 compliant.
<b>Connectors</b>	HDMI receptacle.
<b>LEDs</b>	Power: Blue Input & Output Link: Green
<b>Resolution</b>	480i to 1080p @ 50/60 FPS 1080p @ 24/50/60 FPS 3840 X 2160 @ 24/25/30/60 FPS
<b>Color</b>	8, 10 & 12 bit
<b>Audio</b>	LPCM 7.1CH, Dolby TrueHD, Dolby Atmos, DTS-HD Master Audio and DTS:X
<b>Cable</b>	HDMI cable of appropriate length for video resolution selected.
<b>Power Supply</b>	One (1) 110-240V/5VDC , 2A power supply
<b>Temperature</b>	Operating: 0° to 40°C                      Storage: -20° to 60°C Humidity: up to 90% non-condensing
<b>Enclosure</b>	Metal enclosure
<b>Bracket</b>	Included
<b>Dimensions</b>	4.33" x 2.44" x 1.00" (110 mm x 62 mm x 25 mm)
<b>Weight</b>	0.8 lbs (0.36 Kg)
<b>Compliance</b>	Regulatory: FCC, CE, RoHS
<b>Warranty</b>	2 years
<b>Order Information</b>	500425 HDMI 1X2 Splitter, 4K/60 (UPC: 627699004258)

## Typical Application



### MuxLab Inc.

8495 Dalton Road, Mount Royal, Quebec, Canada, H4T 1V5

Tel: (514) 905 0588 Fax: (514) 905 0589

Toll Free: 1 877 689-5228

E-mail: [videoease@muxlab.com](mailto:videoease@muxlab.com)

[www.muxlab.com](http://www.muxlab.com)