

Portable 2600mAh Mobile Power Bank USB Battery Charger

MODEL NUMBER: **UPB-02K6-1U**



Highlights

- Fits comfortably in your pocket, purse, backpack or laptop bag
- Provides up to 5V, 1A for charging mobile devices
- LED indicates low or full lithium-ion battery
- Charges devices at maximum output up to 2.6 hr.
- Includes USB Micro-B charging cable

Package Includes

- UPB-02K6-1U Portable 2600mAh Mobile Power Bank USB Battery Charger
- USB Micro-B cable, 3 ft.
- Owner's Manual

Description

No more frantic searching for an AC power outlet when your cellphone, tablet or other mobile device's battery power is getting low. The UPB-02K6-1U Portable 2600mAh Mobile Power Bank is the perfect power solution when you're on the road, or stuck somewhere without convenient electricity. It fits comfortably in your pocket, purse, backpack or laptop bag to keep your e-reader, MP3 player, handheld game console or Bluetooth device operating when you need it.

Just connect your device to the UPB-02K6-1U's USB-A port using the included USB Micro-B cable or another cable suitable for your device. The LED indicator will blink to indicate the Mobile Power Bank has enough power to charge the device. The LED will turn off when the Mobile Power Bank's built-in lithium-ion battery drops below 5%.

The portable UPB-02K6-1U provides up to 5V, 1A of power, and its 2600mAh capacity charges devices at maximum power up to 2.6 hours. It protects against short circuits, overvoltage, over-current, overcharges and overdischarges. Charge the Mobile Power Bank by connecting its USB Micro-B port to a USB charger or a computer's USB-A port using the included cable. The blinking LED indicator will turn solid when the battery reaches 100% capacity.

Features

Travel-Sized for Convenient Charging Anywhere

- Fits comfortably in your pocket, purse, backpack or laptop bag
- Ideal for charging cellphones, tablets, e-readers, MP3 players, handheld game consoles and Bluetooth headsets, headphones and speakers
- USB Micro-B charging cable included

Superior Charge Capability Without an AC Power Outlet

- Connect USB-A port to device for charging at maximum output up to 2.6 hr.
- Provides up to 5V, 1A of power at 2600mAh capacity
- Protects against short circuits, overvoltage, over-current, overcharges and overdischarges

Built-In Lithium-Ion Battery

- Connect the power bank's USB Micro-B port to a USB charger or a computer's USB-A port to charge internal battery



- Built-in LED indicates when battery level is 100% or below 5%

Specifications

| OUTPUT | |
|-------------------------------------|----------------------------|
| Charging Ports / Amps | (1) 1A |
| Charging Method | USB |
| PHYSICAL | |
| Unit Dimensions (hwd / in.) | 0.8 x 1.2 x 3.5 |
| Unit Dimensions (hwd / cm) | 2.1 x 3.0 x 9.0 |
| Unit Weight (lbs.) | 0.15 |
| Unit Weight (kg) | 0.07 |
| Color | Black |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32F to 113F (0C to 45C) |
| Storage Temperature Range | 5F to 140F (-15C to 60C) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>