



Omnimate Range - Pitch 3.50 mm





Pin headers SL 3.5/90



Technical Data		VDE	UL	CSA
Rated voltage	V	160*	300	300
Rated current	A	12	10	10

*Overvoltage category III / Pollution severity 3
Additional technical data see page 211



Pin headers SL 3.5/90G



Technical Data		VDE	UL	CSA
Rated voltage	V	160*	300	300
Rated current	A	12	10	10

*Overvoltage category III / Pollution severity 3
Additional technical data see page 211

Pin headers SL 3.5/90F



Technical Data		VDE	UL	CSA
Rated voltage	V	160*	300	300
Rated current	A	12	10	10

*Overvoltage category III / Pollution severity 3
Additional technical data see page 211

Solder pin length		3.2 mm	4.5 mm		
Colour		Orange	Black		
Poles	Type	Cat. No.	Cat. No.	Qty.	
2	SL 3.5/2/90	1597210000	1614130000	100	
3	SL 3.5/3/90	1597220000	1615300000	100	
4	SL 3.5/4/90	1597230000	1615310000	100	
5	SL 3.5/5/90	1597240000	1615320000	50	
6	SL 3.5/6/90	1597250000	1615330000	50	
7	SL 3.5/7/90	1597260000	1615340000	50	
8	SL 3.5/8/90	1597270000	1614140000	50	
9	SL 3.5/9/90	1597280000	1615350000	50	
10	SL 3.5/10/90	1597290000	1615360000	50	
11	SL 3.5/11/90	1597300000	1615370000	50	
12	SL 3.5/12/90	1597310000	1615380000	50	
13	SL 3.5/13/90	1597320000	1615390000	50	
14	SL 3.5/14/90	1597330000	1615400000	50	
15	SL 3.5/15/90	1597340000	1615410000	50	
16	SL 3.5/16/90	1597350000	1614150000	50	
17	SL 3.5/17/90	1618990000	1617820000	20	
18	SL 3.5/18/90	1619000000	1617830000	20	
19	SL 3.5/19/90	1619010000	1617840000	20	
20	SL 3.5/20/90	1619020000	1617850000	20	
21	SL 3.5/21/90	1619030000	1617860000	20	
22	SL 3.5/22/90	1619040000	1617870000	20	
23	SL 3.5/23/90	1619050000	1617880000	20	
24	SL 3.5/24/90	1619060000	1617890000	20	

Accessories	Page
Fixing	195
Marking	196
Coding	199
Miscellaneous	204

Solder pin length		3.2 mm	4.5 mm		
Colour		Orange	Black		
Poles	Type	Cat. No.	Cat. No.	Qty.	
2	SL 3.5/2/90G	1605070000	1614160000	100	
3	SL 3.5/3/90G	1605080000	1615420000	100	
4	SL 3.5/4/90G	1605090000	1615430000	100	
5	SL 3.5/5/90G	1605100000	1614170000	50	
6	SL 3.5/6/90G	1605110000	1615440000	50	
7	SL 3.5/7/90G	1605120000	1615450000	50	
8	SL 3.5/8/90G	1605130000	1614180000	50	
9	SL 3.5/9/90G	1605140000	1615460000	50	
10	SL 3.5/10/90G	1605150000	1615470000	50	
11	SL 3.5/11/90G	1605160000	1615480000	50	
12	SL 3.5/12/90G	1605170000	1615490000	50	
13	SL 3.5/13/90G	1605180000	1615500000	50	
14	SL 3.5/14/90G	1605190000	1615510000	50	
15	SL 3.5/15/90G	1605200000	1615520000	50	
16	SL 3.5/16/90G	1605210000	1614190000	50	
17	SL 3.5/17/90G	1619380000	1617980000	20	
18	SL 3.5/18/90G	1619390000	1617990000	20	
19	SL 3.5/19/90G	1619400000	1618000000	20	
20	SL 3.5/20/90G	1619410000	1618010000	20	
21	SL 3.5/21/90G	1619420000	1618020000	20	
22	SL 3.5/22/90G	1619430000	1618030000	20	
23	SL 3.5/23/90G	1619440000	1618040000	20	
24	SL 3.5/24/90G	1619450000	1618050000	20	

Accessories	Page
Fixing	195
Marking	196
Coding	199
Miscellaneous	204

Solder pin length		3.2 mm	4.5 mm		
Colour		Orange	Black		
Poles	Type	Cat. No.	Cat. No.	Qty.	
2	SL 3.5/2/90F	1607040000	1615530000	100	
3	SL 3.5/3/90F	1607050000	1615540000	100	
4	SL 3.5/4/90F	1607060000	1615550000	100	
5	SL 3.5/5/90F	1607070000	1615560000	50	
6	SL 3.5/6/90F	1607080000	1615570000	50	
7	SL 3.5/7/90F	1607090000	1615580000	50	
8	SL 3.5/8/90F	1607100000	1614200000	50	
9	SL 3.5/9/90F	1607110000	1615590000	50	
10	SL 3.5/10/90F	1607120000	1615600000	50	
11	SL 3.5/11/90F	1607130000	1615610000	50	
12	SL 3.5/12/90F	1607140000	1615620000	50	
13	SL 3.5/13/90F	1607150000	1615630000	50	
14	SL 3.5/14/90F	1607160000	1615640000	50	
15	SL 3.5/15/90F	1607170000	1615650000	50	
16	SL 3.5/16/90F	1607180000	1615660000	50	
17	SL 3.5/17/90F	1619770000	1618280000	20	
18	SL 3.5/18/90F	1619780000	1618290000	20	
19	SL 3.5/19/90F	1619790000	1618300000	20	
20	SL 3.5/20/90F	1619800000	1618310000	20	
21	SL 3.5/21/90F	1619810000	1618320000	20	
22	SL 3.5/22/90F	1619820000	1618330000	20	
23	SL 3.5/23/90F	1619830000	1618340000	20	
24	SL 3.5/24/90F	1619840000	1618350000	20	

Accessories	Page
Fixing	194, 195
Marking	196
Coding	199
Miscellaneous	204