

Mating references and stack heights for
1.27mm pitch, SMT Connectors

Manufacturer's Part Number	Receptacles:			CBEC219-0679B001C1AF	CBEC219-1379B001C1AF	CBEC219-2579B001C1AF	CBEC219-3479B001C1AF	CBEC219-4079B001C1AF	CBED201-0679B001C1AD	CBED201-1379B001C1AD	CBED201-2579B001C1AD	CBED201-3479B001C1AD	CBED201-4079B001C1AD	CBEC220-0679B001C1AF	CBEC220-1379B001C1AF	CBEC220-2579B001C1AF	CBEC220-3479B001C1AF	CBEC220-4079B001C1AF	CBEC201-0679B001C1AF	CBEC201-1379B001C1AF	CBEC201-2579B001C1AF	CBEC201-3479B001C1AF	CBEC201-4079B001C1AF	
				Vertical	Vertical	Vertical	Vertical	Vertical	Horizontal	Horizontal	Horizontal	Horizontal	Horizontal	Vertical	Vertical	Vertical	Vertical	Vertical	Vertical	Vertical	Vertical	Vertical	Vertical	Vertical
Plugs:	Orientation	Height	Ways	9mm	9mm	9mm	9mm	9mm	9.25mm	9.25mm	9.25mm	9.25mm	9.25mm	13.65mm	13.65mm	13.65mm	13.65mm	13.65mm	6.2mm	6.2mm	6.2mm	6.2mm	6.2mm	
				12	26	50	68	80	12	26	50	68	80	12	26	50	68	80	12	26	50	68	80	
GBEC201-0679B001C1AF	Vertical	8.2mm	12	12.2mm					14.4mm					16.85					9.4mm					
GBEC201-1379B001C1AF	Vertical	8.2mm	26		12.2mm					14.4mm					16.85					9.4mm				
GBEC201-2579B001C1AF	Vertical	8.2mm	50			12.2mm					14.4mm					16.85					9.4mm			
GBEC201-3479B001C1AF	Vertical	8.2mm	68				12.2mm					14.4mm					16.85					9.4mm		
GBEC201-4079B001C1AF	Vertical	8.2mm	80					12.2mm					14.4mm					16.85					9.4mm	9.4mm
GBEC202-0679B001C1AF	Vertical	6.7mm	12	10.7mm					12.5mm					15.35mm						7.9mm				
GBEC202-1379B001C1AF	Vertical	6.7mm	26		10.7mm					12.5mm					15.35mm						7.9mm			
GBEC202-2579B001C1AF	Vertical	6.7mm	50			10.7mm					12.5mm					15.35mm						7.9mm		
GBEC202-3479B001C1AF	Vertical	6.7mm	68				10.7mm					12.5mm					15.35mm						7.9mm	
GBEC202-4079B001C1AF	Vertical	6.7mm	80					10.7mm					12.5mm					15.35mm						7.9mm
GBED202-0679B001C1AD	Horizontal	8.2mm	12	14mm					12.8mm					18.65mm						11.2mm				
GBED202-1379B001C1AD	Horizontal	8.2mm	26		14mm					12.8mm					18.65mm						11.2mm			
GBED202-2579B001C1AD	Horizontal	8.2mm	50			14mm					12.8mm					18.65mm						11.2mm		
GBED202-3479B001C1AD	Horizontal	8.2mm	68				14mm					12.8mm					18.65mm						11.2mm	
GBED202-4079B001C1AD	Horizontal	8.2mm	80					14mm					12.8mm					18.65mm						11.2mm