

Range box - AI SORTI BOX RD - 3202960

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

Why buy this product

- ✓ Color coding and the transparent cover facilitate fast access to the required ferrules
- ✓ The practical assortment boxes are designed to keep your workshop tidy
- ✓ Using the integrated euro-clip, they can be hung up on perforated board walls, for example, to save space

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 017918 947132
GTIN	4017918947132
Weight per Piece (excluding packing)	104.500 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Ambient conditions

Short-term temperature	120 °C
Max. permanent temperature	105 °C (-40°C no load / 0°C dynamic load)

General

Color	red
Components	free from silicone and halogen
Flammability rating according to UL 94	HB
Material	E-CU
Coating	tin-plated (galvanic)

Standards and Regulations

Range box - AI SORTI BOX RD - 3202960

Technical data

Standards and Regulations

Connection in acc. with standard	CSA
Flammability rating according to UL 94	HB

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Articles in set

Ferrule - AI 0,5 - 8 WH - 3200014



Ferrule, sleeve length: 8 mm, length: 14 mm, color: white

Ferrule - AI 0,75- 8 GY - 3200519



Ferrule, sleeve length: 8 mm, length: 14 mm, color: gray

Ferrule - AI 1 - 8 RD - 3200030



Ferrule, sleeve length: 8 mm, length: 14 mm, color: red

Ferrule - AI 1,5 - 8 BK - 3200043



Ferrule, sleeve length: 8 mm, length: 14 mm, color: black

Range box - AI SORTI BOX RD - 3202960

Articles in set

Ferrule - AI 2,5 - 8 BU - 3200522



Ferrule, sleeve length: 8 mm, length: 14 mm, color: blue

Classifications

eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201
eCl@ss 8.0	27400218
eCl@ss 9.0	27400218

ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000524
ETIM 6.0	EC000524

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	39121421

Approvals

Approvals

Approvals





CSA / CSAus / EAC / EAC / cCSAus

Ex Approvals

Range box - AI SORTI BOX RD - 3202960

Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	247397
CSAus		http://www.csagroup.org/services-industries/product-listing/	247397
EAC			EAC-Zulassung
EAC			7500651.22.01.00246
cCSAus		http://www.csagroup.org/us/en/services/testing-and-certification/certified-product-listing	
