

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **5046930300**
Status: **Active**
Overview: CP Wire-to-Board and Wire-to-Wire Connector Systems
Description: CP-3.3 Receptacle Housing, 3.30mm Pitch, Single Row, Polarized, Positive Inertia Lock, 3 Circuits, Natural

Documents:

| | |
|---|---|
| 3D Model | Application Specification AS-504693-002-001 (PDF) |
| Drawing (PDF) | Packaging Specification SPK-504693-001-001 (PDF) |
| Product Specification PS-504693-001-001 (PDF) | RoHS Certificate of Compliance (PDF) |
| Application Specification AS-504693-001-001 (PDF) | Product Literature (PDF) |

General

| | |
|-----------------------------|---|
| Product Family | Crimp Housings |
| Series | 504693 |
| Application | Signal, Wire-to-Wire |
| Overview | CP Wire-to-Board and Wire-to-Wire Connector Systems |
| Product Literature Order No | 987651-6581 |
| Product Name | CP-3.3 |
| UPC | 887191484426 |

Physical

| | |
|-------------------------------|-----------------|
| Circuits (maximum) | 3 |
| Color - Resin | Natural |
| Gender | Receptacle |
| Glow-Wire Compliant | No |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Resin | PBT |
| Net Weight | 1055.000/mg |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 3.30mm |
| Pitch - Termination Interface | 3.30mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40°C to +105°C |

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|--------------------------------------|
| Application Specification | AS-504693-001-001, AS-504693-002-001 |
| Packaging Specification | SPK-504693-001-001 |
| Product Specification | PS-504693-001-001 |
| Sales Drawing | SD-504693-001 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[504693 Series](#)

Mates With

Plug Housing [504694-0300](#)

Use With

Terminal Retainer [504695](#) . Receptacle Crimp Terminal [50397](#) , [505607](#)