

# 00 21 40

## Tool Case "BIG Twin" Electric 65-part



- Equipped with 65 brand name quality tools, some VDE-tested according to DIN EN 60900
- Hard-wearing ABS hard-shell construction with aluminium frame and circular buffer protection
- Comfortable handle and mounting device for a "Trolley" embedded in the bottom (available ordering ref. 00 21 40 T)
- Can be opened on one or both sides; bottom tray and cover can be opened independently
- Stands stable in any opening position due to lid-holders and hinge mechanisms on both sides, that register in a position of 45° and 90°
- 3-digit lock and two flip-locks for fixation of the cover
- Removable document compartment and removable tool board, with 13 push-in compartments on one side
- Base tray, height 58 mm, can be subdivided by flexible inserts; cover plate with six large push-in compartments, can be fixed by press button
- Dimensions, exterior (W x H x D): 490 x 255 x 410 mm dimensions, interior (W x H x D): 445 x (105 + 105) x 350 mm

<b>Article No.</b>	00 21 40
<b>EAN</b>	4003773081968
<b>Net weight g</b>	11400

technical change and errors excepted

### Content 00 21 40 (21)

Article No.			Quantity	Nominal size	
00 11 01	Knipex	KNIPEX TwinKey®, for all standard cabinets and shut-off systems	1		
08 26 145	Knipex	Needle-Nose Combination Pliers	1		
12 42 195	Knipex	KNIPEX MultiStrip 10, Automatic Insulation Stripper	1		
13 86 200	Knipex	Pliers for Electrical Installation	1		
16 95 01 SB	Knipex	KNIPEX ErgoStrip®, Universal Dismantling Tool	1		
26 26 200	Knipex	Snipe Nose Side Cutting Pliers, (Stork Beak Pliers)	1	200 mm	
70 06 160	Knipex	Diagonal Cutter	1	160 mm	
74 06 200	Knipex	High Leverage Diagonal Cutter	1	200 mm	
86 03 180	Knipex	Pliers Wrench, pliers and a wrench in a single tool	1	180 mm	
87 01 180	Knipex	KNIPEX Cobra®, Hightech Water Pump Pliers	1	180 mm	
97 53 04	Knipex	Self-Adjusting Crimping Pliers for End Sleeves (ferrules), with lateral access	1		
98 52	Knipex	Cable Knife	1	185 mm	
98 25 01 SL	Knipex	Screwdriver (Slim) for cross-recessed screws, Pozidriv®	1		
98 20 35 SL	Knipex	Screwdriver (Slim) for slotted screws	1		
05003484001	Wera	16-part set of VDE interchangeable blades, slim	1		
004018	Wera	8100 SA 8 Zyklus set of metal ratchets, 28 parts	1	1/4"	
003760	Wera	Joker open-end wrench	1	10 x 13 mm	
101-0300	Picard	Locksmith's hammer	1	300 g	
361 252 1	Rennsteig	Electrician's Chisel	1	250 x 10 mm	
16135	Stabila	Model 70 Electric spirit level	1	430 mm	
18115	Stabila	Pocket Electric mini spirit level	1	68 mm	

**Spare Parts**

<b>Article No.</b>	<b>EAN</b>	
00 21 99 V05	4003773082088	

**Accessories**

<b>Article No.</b>	<b>EAN</b>	
00 21 40 LE	4003773057673	Tool Case "BIG Twin" empty
00 21 40 T	4003773062981	Trolley for rolling case transport