


Produktname | *Product name*: M200F  
 Artikelnummer | *Part Number*: 1600-0173  
 Anfragenummer | *Inquiry Number*: AN201617  
 Ersteller / Datum | *Creator / Date*: LHE / 2017-02-13

Version	Change	Date	Name
V0	---	2017-02-13	LHE

Template name: Light (Non-Rechargeable), Template version: V5

Leuchte / light



**Technische Daten der Leuchte / technical data of the light:**



Haupt-LED-Leuchtmittel:	5W LED (Fokussierbar)	Main LED illuminant:	5W LED (Focus able)
Schalterfunktion:	1. schalten: 100% LED	Switch function:	1. switch: 100% LED
	2. tippen: 30%		2. tap: 30%
	3. tippen :Strobe		3. tap: strobe
	4. schalten: Aus		4. switch: Off

Lichtstrom: [Lumen] 100% 30%	240lm 80lm	Luminous flux (light output): [Lumen] 100% 30%	240lm 80lm
Leuchtdauer: 100% 30%	ca. 7h 30min ca. 22h 00min	Run time: 100% 30%	approx. 7h 30min approx. 22h 00min
Leuchtweite: 100% 30%	120m 65m	Beam distance: 100% 30%	120m 65m
Maximale Beleuchtungsstärke: [Lux] 100%: 30%:	3000lx (Abstand:1m) 1000lx (Abstand:1m)	Peak beam illuminance: [Lux] 100%: 30%:	3000lx (Distance:1m) 1000lx (Distance:1m)
Risikogruppe (EN 62471; Bewertet nach DIN IEC/TR 62778 Anhang C.2)	2	Risk group (EN 62471; Assessed with TR 62778 Annex C.2)	2

Benötigte Zellen:	2x AA Mignon 1.5V Batterien (Alkaline; LR6/AM3/MN1500)	Battery:	2x AA Mignon 1.5V batteries (Alkaline; LR6/AM3/MN1500)
Schutzart des Gehäuses:	IP54	Degree of protection by the enclosure:	IP54
Gehäusematerial:	Aluminium	Housing material:	Aluminium
Betriebstemperatur:	-10°C...25°C	Operating temperature:	-10°C...25°C
Lagertemperatur:	-10°C...50°C (Nur Alkaline Batterie/Batterien) -20°C...70°C (Nur Lampe)	Storage temperature:	-10°C...50°C (Alkaline battery/batteries only) -20°C...70°C (Torch only)
Empfohlene Lagerbedingungen: (Nur Alkaline Batterien)	Temperatur: 5..25°C Luftfeuchtigkeit: 45..75%	Recommended storage conditions: (Alkaline batteries only)	Temperature: 5...25°C Rel. humidity: 45...75 %
Approbationen:	CE	Approvals:	CE
Gewicht:	129g nur die Lampe 174g mit 2 x Batterien (wie oben beschrieben)	Weight:	129g only the torch 174g with 2 x batteries (as described above)
Lieferumfang:	- 2 x Batterien (wie oben beschrieben)	Shipment:	- 2 x batteries (as described above)

	- Tragegurt - Gürtelclip		- <i>Lanyard</i> - <i>Belt clip</i>
Verpackung:	Blister-Verpackung	Package:	<i>Blister shell</i>