

# PG Nylon Cable Gland

pro-POWER


RoHS  
Compliant



## Features

- High grade nylon cable glands
- Available in grey
- IP65 rating
- Low smoke
- Halogen free
- Lock nut included
- Sealing: Ding qing rubber
- CE compliant

## Diagram



## Dimension Table

Part Number	Size (mm)	GL (mm)	H (mm)
PG7DG	3-6.5	8	22
PG9DG	4-8	8	26
PG11DG	5-10	8	27
PG13DG	6 to 12	9	28
PG16DG	10 to 14	10	30
PG21DG	13 to 18	10	35
PG29DG	18 to 25	12	40

## Part Number Table

Description	Pack Quantity	Part Number
PG7 Nylon Cable Gland Grey	10 pcs	PG7DG
PG9 Nylon Cable Gland Grey		PG9DG
PG11 Nylon Cable Gland Grey		PG11DG
PG13.5 Nylon Cable Gland Grey		PG13DG
PG16 Nylon Cable Gland Grey		PG16DG
PG21 Nylon Cable Gland Grey		PG21DG
PG29 Nylon Cable Gland Grey		PG29DG

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com  
www.farnell.com  
www.newark.com  
www.cpc.co.uk

pro-POWER

## Part Number Table

Description	Part Number

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.