



Actual

Catalog Number: GSB058
Product ID: 7TAI029070R0002
UPC Number: 78621081276
EAN Number: 05414363113522
Status: Active

Two Piece Inner Sleeve Connector for Hexagonal Range, Length 5/16 Inch/7.9mm, Inner Diameter .058 Inches/1.47mm, Outer Diameter .083 Inches/2.10mm, Color Yellow, Hard Bronze, Tin Plated

- Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Inner sleeve for the Hexagonal Range (the corresponding outer sleeve is crimped with a hand tool and the result is a hexagonal-shaped crimp), for grounding shielded and coaxial cables.
- The sleeves are color coded according to their size.
- Millions of installations in communications, aerospace, electronic, telephone, radio and TV applications.

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Shield-Kon
Type	Two-Piece Inner Sleeve Connector
Special Features	Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Inner sleeve for the Hexagonal Range (the corresponding outer sleeve is crimped with a hand tool and the result is a hexagonal-shaped crimp), for grounding shielded and coaxial cables. The sleeves are color coded according to their size. Millions of installations in communications, aerospace, electronic, telephone, radio and TV applications.
Material	Hard Bronze
Color	Yellow

European Specifications (ETIM)

ETIM	EC002650 Connection for screened wires
Model	2-part
Sleeve form	Internal sleeve
Insulated	N
Outer diameter sleeve	2.1mm
Inner diameter sleeve	1.47mm
Sleeve length	7.9mm
Colour code	Yellow
Compression shape	Hexagon
Reel packaging	N

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	2.09x1.1x2.9
Outer Quantity	10000
Outer Dimensions (inches)	6x3.2x2.1
Weight Uom	0.63 lbs. per 1000

Documents / Support Tools

Technical Data Sheet Global	wsd-000206
-----------------------------	------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com