



21-Piece Express Ratchet Screwdrivers



No. 70210



No. 70211



21-PIECE EXPRESS RATCHET SCREWDRIVER
Drive Screws Twice as Fast!

21-PIECE T-HANDLE EXPRESS RATCHET SCREWDRIVER
Drive Screws Twice as Fast!

Features:

- Patented ratcheting mechanism helps drive the screws 2 times faster than regular screwdriver
- To achieve double efficiency, simply hold the collar and rotate the handle clockwise and counter clockwise
- Convenient slider switch reverses direction
- Twenty (20) 4mm (5/32 in.) Hex Shank Precision Bits

Features:

- Patented ratcheting mechanism helps drive the screws 2 times faster than regular screwdriver
- To achieve double efficiency, simply hold the collar and rotate the handle clockwise and counter clockwise
- Convenient slider switch reverses direction
- Twenty (20) 4mm (5/32 in.) Hex Shank Precision Bits

Includes:

- 4 Slotted Tips: 1/16" (1.5mm), 5/64" (2mm), 3/32" (2.5mm), 1/8" (3mm)
- 4 Phillips Tips: #000, #00, #0, #1
- 9 Torx® Tips: T3, T4, T5, T6, T7, T8, T9, T10, T15
- 3 Pozidrive Tips: PZ00, PZ0, PZ1

Includes:

- 2 Slotted Tips: 1.5mm, 2.5mm
- 2 Phillips Tips: PH00, PH1
- 3 Star Tips: T5, T6, T10
- 3 Socket Tips: 3/32", 1/8", 5/32"
- 5 Hex SAE Tips: 1/16", 5/64", 3/32", 1/8", 5/32"
- 5 Hex Metric Tips: 4mm, 3mm, 2.5mm, 2mm, 1.5mm



Slotted
1/16" (1.5mm),
5/64" (2mm),
3/32" (2.5mm),
1/8" (3mm)



Phillips
#000,
#00,
#0,
#1



Torx®
T3, T4, T5,
T6, T7,
T8, T9,
T10, T15



Pozidrive
PZ00,
PZ0,
PZ1



Slotted
1.5mm
2.5mm



Phillips
PH00
PH1



Torx®
T5, T6,
T10



Socket
3/32",
1/8",
5/32"



Hex SAE
1/16",
5/64",
3/32",
1/8",
5/32"



Hex Metric
4mm, 3mm,
2.5mm,
2mm,
1.5mm



General Tools & Instruments

80 White Street, New York, NY 10013-3567

TEL: 212. 431. 6100 TOLL FREE: 800. 697. 8665

sales@generaltools.com www.generaltools.com

70210/70211SS Printed in USA 04/23/15



General Tools & Instruments



GeneralToolsNYC