

Universe	Professional
Type	Lighting
Category	Ultra-compact headlamps
Subcategory	Ultra-compact headlamps



Hybrid
CONCEPT

TACTIKKA® CORE


The TACTIKKA CORE headlamp offers 350 lumen brightness. It is ideal for close-range work, as well as for moving around. Featuring a mixed beam, it ensures wide, focused or red stealth lighting. A HYBRID headlamp that comes with CORE, a battery that is rechargeable via standard USB port. It is compatible with standard AAA/LR03 batteries (not included) without the need for an adapter.



Multi-beam headlamp designed for proximity lighting, movement, and distance vision. White and red lighting for nocturnal stealth.



Simple charge via battery via the micro USB port.



TACTIKKA CORE is a HYBRID headlamp: it comes with the CORE rechargeable battery, and is also compatible with three AAA/LR03 batteries.



Adjustable elastic headband with emergency whistle.

Short Description Compact multi-beam headlamp with red lighting and CORE rechargeable battery. 350 lumens

- Selling Points**
- Powerful (350 lumens), versatile headlamp
 - Headlamp comes with the CORE rechargeable battery, for an economical and sustainable solution, with 300 guaranteed charging cycles
 - TACTIKKA CORE is a HYBRID headlamp: it comes with the CORE rechargeable battery, and is also compatible with three AAA/LR03 batteries
 - Two beam patterns (wide or mixed) and several lighting modes meet the need for high-performance lighting when working in the dark: proximity or distance vision and movement
 - Red lighting preserves night vision and stealth
 - Headband equipped with emergency whistle

-
- Specification**
- Light output: 350 lumens
 - Weight: 82g
 - Beam pattern: wide or mixed
 - Energy: 1250 mAh CORE rechargeable battery (included)
 - Battery compatibility: alkaline, lithium and Ni-MH
 - Certification(s): CE
 - Watertightness: IP X4 (weather resistant)
-

Lighting performance

Lighting color	Lighting modes	Brightness	Distance	Burn time	Reserve mode
white	MAX AUTONOMY	5 lm	7 m	160 h	-
	STANDARD	100 lm	50 m	7 h	3 h at 5 lm
	MAX POWER	350 lm	95 m	2 h	
red	proximity	2 lm	6 m	40 h	-
	strobe	visible at 700 m for 350 h			

Specifications by reference

Reference(s)	E99ADA
Color(s)	black
Made in	FR
Guarantee	5 years
Packing	1
Case quantity	50
EAN	3342540815735

Accessory(ies) KIT ADAPT
 FIXATION TACTIKKA®
 CORE

Related product(s) ALVEO VENT
 VERTEX® BEST