


94172




Complete units type XD2 G, with chromium plated metal bezel

Interchangeable contacts


Description	Operation	Spring return to zero position	Bezel finish	Reference	Weight kg
2 direction Fixing centres 90 x 90 mm	1 notch 1 N/O contact per direction	Without	Shiny	XD2 GA8211	0.300
			Black	XD2 GA82117	0.300
		With	Shiny	XD2 GA8221	0.300
			Black	XD2 GA82217	0.300
	2 notches 2 N/O contacts per direction	Without	Shiny	XD2 GA8231	0.500
			Black	XD2 GA82317	0.500
		With	Shiny	XD2 GA8241	0.500
			Black	XD2 GA82417	0.500
	1 st notch stay put 2 nd notch with spring return to 1 st notch	Shiny	XD2 GA8251	0.500	
		Black	XD2 GA82517	0.500	




94173




4 direction Fixing centres 90 x 90 mm	1 notch 1 N/O contact per direction	Without	Shiny	XD2 GA8411	0.330
			Black	XD2 GA84117	0.330
		With	Shiny	XD2 GA8421	0.330
			Black	XD2 GA84217	0.330
	2 notches 2 N/O contacts per direction	Without	Shiny	XD2 GA8431	0.550
			Black	XD2 GA84317	0.550
		With	Shiny	XD2 GA8441	0.550
			Black	XD2 GA84417	0.550
	1 st notch stay put 2 nd notch with spring return to 1 st notch	Shiny	XD2 GA8451	0.550	
		Black	XD2 GA84517	0.550	



XD2 GA8441



ZD2 GY5201



ZD2 GY6201



ZB2 BE101

Legend plates

Description	Text	Colour	Reference	Weight kg
2 direction 40 x 64 mm	Without	Black one side, red reverse	ZD2 GY5201	0.002
		White one side, yellow reverse	ZD2 GY5401	0.002
	With (1) (specify when ordering)	Black background, white letters	ZD2 GY5002	0.002
		Red background, white letters	ZD2 GY5004	0.002
		White background, black letters	ZD2 GY5001	0.002
		Yellow background, black letters	ZD2 GY5005	0.002
4 direction 64 x 64 mm	Without	Black one side, red reverse	ZD2 GY6201	0.003
		White one side, yellow reverse	ZD2 GY6401	0.003
	With (1) (specify when ordering)	Black background, white letters	ZD2 GY6002	0.003
		Red background, white letters	ZD2 GY6004	0.003
		White background, black letters	ZD2 GY6001	0.003
		Yellow background, black letters	ZD2 GY6005	0.003

Contact block

Description	Contact	Reference	Weight kg
Slow break Additional or replacement	N/O	ZB2 BE101	0.015

(1) 2 lines of 11 characters maximum per direction.

Other versions

XD2 G joystick controllers with:

- variable composition; 2, 3, 4 or 8 direction,
- contact blocks with Faston connectors conforming to NF C 20-120,
- gold flashed contacts for low power switching.

Please consult your Customer Care Centre.