

3 m (10 ft.) USB-C to DisplayPort Cable - 4K 60Hz - Black

Product ID: CDP2DPMM3MB



This USB-C™ to DisplayPort adapter cable offers a convenient solution for directly connecting your DisplayPort over USB Type-C™ device to your DP monitor or projector. The adapter offers a connection distance of up to 3 m (10 ft.) and works with USB-C devices that support DP Alt Mode, such as the MacBook, Chromebook Pixel™ and Dell™ XPS™ models 15 and 13. It's also compatible with Thunderbolt™ 3 ports.

Clutter-free installation

At 3 m (10 ft.) in length, this adapter cable delivers a direct connection that eliminates excess adapters and cabling, ensuring a tidy, professional installation.

For shorter installations, StarTech.com also offers a [1 m \(3 ft.\) USB-C to DisplayPort cable \(CDP2DPMM1MB\)](#) and [1.8 m \(6 ft.\) USB-C to DisplayPort cable \(CDP2DPMM6B\)](#), enabling you to choose the right cable length for your custom installation needs.

Astonishing picture quality

At four times the resolution of high-definition 1080p, you'll be amazed at the picture quality of a 4K 60Hz monitor or television. This adapter cable lets you harness the video capabilities that are built into your USB Type-C connection, to deliver the astonishing quality of Ultra HD to your 4K display.

Plus, the adapter is still compatible with lower display resolutions, such as 1080p, which makes it a great accessory for your current home, office or other HD work environment, while future-proofing for 4K 60Hz implementation.

The CDP2DPMM3MB is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect a USB Type-C computer to a DisplayPort projector or display in your classroom, auditorium or boardroom
- Install at your home workstation or office hot desk to make your USB-C computer compatible with your DisplayPort monitor

Features

- Position your devices as needed throughout your workspace, with reduced cable clutter
- 3 m (10 ft.) all-in-one solution with a combined cable and adapter
- Hassle-free connection with the reversible USB-C connector
- Astonishing video quality with support for resolutions up to 4K at 60Hz

Hardware	Warranty	2 Years
	Adapter Style	Cable Adapters
	Chipset ID	STMicroelectronics - STM32F072CBU6 PERICOM - PI3DPX1203
	Converter Type	Cable Adapters
	Output Signal	DisplayPort
	Ports	1
Performance	Audio Specifications	7.1 surround sound
	Maximum Digital Resolutions	3840x2160 @ 60 Hz
	Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1920x1080 (High-definition 1080p) 1920x1200 2560x1440 2560x1600 3840x2160 (Ultra HD 4K)
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
	Connector B	1 - DisplayPort (20 pin) Male Output
Special Notes / Requirements	Note	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
Environmental	Humidity	20%-70%RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-40°C to 80°C (-40°F to 158°F)
Physical Characteristics	Color	Black
	Product Height	15 mm [0.6 in]
	Product Length	3000 mm [118.1 in]
	Product Weight	222 g [7.8 oz]
	Product Width	20 mm [0.8 in]
Packaging Information	Shipping (Package) Weight	231 g [8.2 oz]
What's in the Box	Included in Package	1 - USB-C to DisplayPort cable

Product appearance and specifications are subject to change without notice.