


DATEC MOBIL BOXES

- Award winning ergonomic design
- Three sizes L, M & S
- Ideal for hand held and desktop instruments and measuring devices
- IP65 protection class with optional seal - uniquely including the battery compartments
- Strong screw together assembly
- Available with or without display window cutouts
- Battery compartments included on L & S - optional on M using the battery cradle accessories
- Internal mounting pillars for pcb's
- L accepts Eurocards 100x160mm size
- Material ABS UL94 HB
- Colours off-white RAL 9002 or black RAL 9005



TYPE I
without display window cutout

TYPE II
with display window cutout

SUPPLY

- Top
- Base
- Battery compartment lid
- Rubber feet
- Screw kit

BATTERY COMPARTMENTS

SIZE L
accepts one 9V PP3 cell or four 1.5V AA cells

SIZE M
optional battery cradles for 1 9V PP3 cell, 2 9V PP3 cells and 4 1.5V AA cells.
See accessories table.

SIZE S
accepts one 9V PP3 cell or two 1.5V AA cells

BATTERY CLIPS

Order suitable clips/contacts, from accessory table to suit batteries being fitted. A foam spacer is available to secure AA cells in the compartment - required due to the difference in height between PP3 and AA cells.


IP65 SEALING KITS

For sealing the case and battery compartment to IP65. Includes two O rings and sealing washers.

ACRYLIC DISPLAY WINDOWS

These provide protection for LCD modules and IP65 sealing in the window area. A border is printed on the windows in pebble grey or black to suit the case colours.

TILT FOOT BAR



Useful accessory for tilting size M & S to improve the viewing angle when used on a desk. Non-slip feet available to reduce slipping on the desk surface.

Part No. Case

Size	Colour	Type	L	W	D	Display window	
A 90 75 107	L	Off-white	I	252	121	50	-
A 90 75 207	L	Off-white	II	252	121	50	74.6 x 24.2
A 90 75 109	L	Black	I	252	121	50	-
A 90 75 209	L	Black	II	252	121	50	74.6 x 24.2
A 90 74 107	M	Off-white	I	195	101	44	-
A 90 74 207	M	Off-white	II	195	101	44	60 x 15
A 90 74 109	M	Black	I	195	101	44	-
A 90 74 209	M	Black	II	195	101	44	60 x 15
A 90 73 107	S	Off-white	I	152	83	33.5	-
A 90 73 207	S	Off-white	II	152	83	33.5	45.6 x 17.7
A 90 73 109	S	Black	I	152	83	33.5	-
A 90 73 209	S	Black	II	152	83	33.5	45.6 x 17.7

Part No. Accessory

For case	Description
L	IP65 Sealing kit
M	IP65 Sealing kit
S	IP65 Sealing Kit
L	Battery clips for 4 AA cells
M	Battery cradle for 1 9V PP3 cell
M	Set of battery clips for 1 9V PP3 cell
M	Battery cradle for 2 9V PP3 cells
M	Set of battery clips for 2 9V PP3 cells
M	Battery cradle for 4 AA cells
M	Battery clips for 4 AA cells
S	Battery clips for 2 AA cells
L&S	Battery contact for PP3 cell
L	Pebble grey display window
L	Black display window
M	Pebble grey display window
M	Black display window
S	Pebble grey display window
S	Black display window
M&S	Off-white tilt foot bar
M&S	Black tilt foot bar
M&S	Non-slip feet for tilt foot bar (Pkt 2)
All	Foam spacer for securing AA cells