

Filament LED

- Easy Replacement
- Flicker Free Design
- Even Light Distribution
- True Retro Fit
- Automated Production
- IC Drivers
- Instant Light

- Replacements for 25w, 40w and 60w Incandescent
- Dimmable Alternatives
- 2700K Output
- Clear and Opal Alternatives



GLS - 40W REPLACEMENT - 15,000 HOURS

Part Number	Pack	Watt.	Cap	Dimmable	Life	Lumen	Colour Temp.	Lamp Dims.	Inner Qty.	Outer Qty.
S9023	Blister	4.3w	B22	x	15000 hrs	470lm	2700K	60x109	10	40
S9024	Blister	4.3w	E27	x	15000 hrs	470lm	2700K	60x109	10	40

GLS - 60W REPLACEMENT - 15,000 HOURS

Part Number	Pack	Watt.	Cap	Dimmable	Life	Lumen	Colour Temp.	Lamp Dims.	Inner Qty.	Outer Qty.
S9025	Blister	6.2w	B22	x	15000 hrs	806lm	2700K	60x109	10	40
S9026	Blister	6.2w	E27	x	15000 hrs	806lm	2700K	60x109	10	40

CANDLE - 25W REPLACEMENT - 15,000 HOURS

Part Number	Pack	Watt.	Cap	Dimmable	Life	Lumen	Colour Temp.	Lamp Dims.	Inner Qty.	Outer Qty.
S9027	Blister	2.4w	E14	x	15000 hrs	250lm	2700K	35x98	12	72
S9028	Blister	2.4w	B22	x	15000 hrs	250lm	2700K	35x98	12	72

CANDLE - 40W REPLACEMENT - 15,000 HOURS

Part Number	Pack	Watt.	Cap	Dimmable	Life	Lumen	Colour Temp.	Lamp Dims.	Inner Qty.	Outer Qty.
S9029	Blister	4w	B22	x	15000 hrs	470lm	2700K	35x98	12	72
S9030	Blister	4w	E14	x	15000 hrs	470lm	2700K	35x98	12	72
S9031	Blister	4w	E27	x	15000 hrs	470lm	2700K	35x98	12	72

GOLF - 40W REPLACEMENT - 15,000 HOURS

Part Number	Pack	Watt.	Cap	Dimmable	Life	Lumen	Colour Temp.	Lamp Dims.	Inner Qty.	Outer Qty.
S9032	Blister	4w	E27	x	15000 hrs	470lm	2700K	45x75	12	72
S9033	Blister	4w	E14	x	15000 hrs	470lm	2700K	45x75	12	72