

Description

The CiT elite is a budget focused Micro-ATX chassis aimed at business and home office solutions. The Elite is one of the best air cooling solutions with a full mesh front panel for a professional look and is equipped with a USB3 port on the front of the I/O panel. The Elite also includes a rear 80mm fan.

The Elite is an ideal choice for anyone looking to build an office or home based PC on a budget.

Key Features

- Full mesh front panel with 1 x USB 3.0
- Black chassis with 80mm rear cooling fan included
- Micro ATX chassis with a simple design
- Intel Approved TAC2.0 thermal chassis
- Black coated interior

Specifications

PSU Rail Output (max.):

+3.3V: 26A
+5V: 27A
+12V: 22A
-12V: 0.5A
+5VSB: 2.0A

PSU Connectors & Qty:

20 + 4pin ATX Mainboard: 1
4pin +12V CPU: 1
SATA: 3
4pin Molex: 2
FDD: 1
:

**Chassis Size
(Without the Front panel and Side Panel):** (W) 173 x (H) 370 x (D) 365mm

Case Specifications

Form Factor: Micro ATX

Motherboard Support: Micro ATX, Mini ITX

PSU Support: Standard ATX

PSU Location: Top

Gaming Case: No

Water Cooling: Not Water Cooling Ready

Body Material: 0.5mm SPCC

Front Bezel Material: Mesh

Side Panel: Vented

Internal Cable Management Depth: 21mm

External Bays: 2 x 5.25" External
2 x 3.5" External

Internal Bays: 1 x 3.5" Internal
2 x 2.5" Internal

Drive Bay Notes:

Expansion Slots: 4 x Full Size

Cooling Front: Space for 1 x 80mm Fan

Cooling Top: None

Cooling Rear: 1 x 80mm Fan (1 x 80mm Fan inc.)

Cooling Side: Vent

Cooling Bottom: None

1 x USB 3.0

IO Ports: 1 x USB 2.0

1 x HD Audio

GPU Max Length: 330mm

CPU Cooler Maximum Height: 160mm

Front Bezel Colour: Black

Body Colour: Black

System Cabinet Features: Supports Kensington Lock

PSU Included: Yes

General Specifications

Manufacturer Elite

Part Number:

EAN Number: 5055492406101

Has Mains Plug: No

Colour: Black

What's In The Case

Box: Screws

Unit (Product)

Dimensions (mm): 173mm x 414mm x 371mm (W x H x D)

Packaging

Dimensions (mm): 209mm x 445mm x 405mm (W x H x D)

Net Weight (KGs): 4.2 KGs

Gross Weight (KGs): 4.8 KGs