

Thermal transfer printer set - THERMOFOX SET - 0803986

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Portable thermal transfer printer for materials off the roll, with accessories (adapter, battery, USB cable, MM-EMLF (18XE) WH/BK and EMLC (18xE) WH/BK materials) in hard-shell case

Why buy this product

- ✓ Maintenance-free operation with proven thermal transfer printing technology
- ✓ Easy to control with the CLIP PROJECT software
- ✓ Printing of self-adhesive, non-sticky labels and shrink sleeves
- ✓ The THERMOFOX prints materials in cassette format, which contain the material to be marked and the appropriate ink ribbon.
- ✓ Intuitive user guidance thanks to a well-structured menu and direct input keys
- ✓ 8 different barcodes and over 300 symbols can be integrated.
- ✓ Alternative control via the CLIP PROJECT software

Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 212609
GTIN	4055626212609
Weight per Piece (excluding packing)	2,259.000 g
Custom tariff number	84433210
Country of origin	China

Technical data

General

Interface	USB
Weight	656 g

Dimensions

Length	230 mm
Height	98 mm
Width	69 mm

Thermal transfer printer set - THERMOFOX SET - 0803986

Technical data

Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC
Additional text	50/60 Hz

Classifications

eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201
eCl@ss 8.0	19140104
eCl@ss 9.0	19140104

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000005
ETIM 5.0	EC001672
ETIM 6.0	EC001672

UNSPSC

UNSPSC 6.01	27121706
UNSPSC 7.0901	27121706
UNSPSC 11	27121706
UNSPSC 12.01	27121706
UNSPSC 13.2	43212108

Approvals

Approvals

Approvals

EAC / KC

Ex Approvals

Approval details

Thermal transfer printer set - THERMOFOX SET - 0803986

Approvals

EAC			RU D- DE.ME06.B.02060
-----	--	--	--------------------------

KC		http://eng.kcc.go.kr/user/ehpMain.do	MSIP-REM-YG3
----	--	---	--------------

Accessories

Accessories

Conductor marking

Cable marker label - MM-WML 3 (EX10)R C1 WH/BK - 0803931



Cable marker label, Roll, white, can be labeled with: THERMOFOX: without print, mounting type: adhesive, lettering field size: continuous x 10 mm

Cable marker label - MM-WML 5 (EX10)R C1 WH/BK - 0803932



Cable marker label, Roll, white, can be labeled with: THERMOFOX: without print, mounting type: adhesive, lettering field size: continuous x 10 mm

Device marking

Label, highly flexible - MM-EMLF (EX18)R C1 GN/WH - 0803953



Highly flexible label, continuous, cassette, green with white imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX24)R C1 GN/WH - 0803954



Highly flexible label, continuous, cassette, green with white imprint, mounting type: adhesive, can be marked with THERMOFOX

Thermal transfer printer set - THERMOFOX SET - 0803986

Accessories

Label, highly flexible - MM-EMLF (EX10)R C1 OG/BK - 0803955



Highly flexible label, continuous, cassette, orange with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX12)R C1 OG/BK - 0803956



Highly flexible label, continuous, cassette, orange with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX18)R C1 OG/BK - 0803957



Highly flexible label, continuous, cassette, orange with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX24)R C1 OG/BK - 0803958



Highly flexible label, continuous, cassette, orange with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX10)R C1 RD/WH - 0803959



Highly flexible label, continuous, cassette, red with white imprint, mounting type: adhesive, can be marked with THERMOFOX

Thermal transfer printer set - THERMOFOX SET - 0803986

Accessories

Fabric label - MM-EMLC (EX10)R C1 WH/BK - 0803933



Highly flexible textile label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Fabric label - MM-EMLC (EX12)R C1 WH/BK - 0803934



Highly flexible textile label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Fabric label - MM-EMLC (EX18)R C1 WH/BK - 0803936



Highly flexible textile label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX10)R C1 WH/BK - 0803937



Highly flexible label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX12)R C1 WH/BK - 0803938



Highly flexible label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Thermal transfer printer set - THERMOFOX SET - 0803986

Accessories

Label, highly flexible - MM-EMLF (EX18)R C1 WH/BK - 0803939



Highly flexible label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX24)R C1 WH/BK - 0803940



Highly flexible label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX10)R C1 YE/BK - 0803941



Highly flexible label, continuous, cassette, yellow with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX12)R C1 YE/BK - 0803942



Highly flexible label, continuous, cassette, yellow with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX18)R C1 YE/BK - 0803943



Highly flexible label, continuous, cassette, yellow with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Thermal transfer printer set - THERMOFOX SET - 0803986

Accessories

Label, highly flexible - MM-EMLF (EX24)R C1 YE/BK - 0803944



Highly flexible label, continuous, cassette, yellow with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX10)R C1 BU/WH - 0803945



Highly flexible label, continuous, cassette, blue with white imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX12)R C1 BU/WH - 0803946



Highly flexible label, continuous, cassette, blue with white imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX18)R C1 BU/WH - 0803947



Highly flexible label, continuous, cassette, blue with white imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX24)R C1 BU/WH - 0803949



Highly flexible label, continuous, cassette, blue with white imprint, mounting type: adhesive, can be marked with THERMOFOX

Thermal transfer printer set - THERMOFOX SET - 0803986

Accessories

Label, highly flexible - MM-EMLF (EX10)R C1 GN/WH - 0803950



Highly flexible label, continuous, cassette, green with white imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX12)R C1 GN/WH - 0803952



Highly flexible label, continuous, cassette, green with white imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX12)R C1 RD/WH - 0803960



Highly flexible label, continuous, cassette, red with white imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX18)R C1 RD/WH - 0803961



Highly flexible label, continuous, cassette, red with white imprint, mounting type: adhesive, can be marked with THERMOFOX

Label, highly flexible - MM-EMLF (EX24)R C1 RD/WH - 0803962



Highly flexible label, continuous, cassette, red with white imprint, mounting type: adhesive, can be marked with THERMOFOX

Thermal transfer printer set - THERMOFOX SET - 0803986

Accessories

Insert label - MM-EMT (EX6)R C1 WH/BK - 0803963



Insert label, continuous, cassette, white with black imprint, mounting type: slide-in, can be marked with: THERMOFOX

Insert label - MM-EMT (EX8)R C1 WH/BK - 0803965



Insert label, continuous, cassette, white with black imprint, mounting type: slide-in, can be marked with: THERMOFOX

Insert label - MM-EMT (EX15)R C1 WH/BK - 0803966



Insert label, continuous, cassette, white with black imprint, mounting type: slide-in, can be marked with: THERMOFOX

Insert label - MM-EMT (EX17)R C1 WH/BK - 0803967



Insert label, continuous, cassette, white with black imprint, mounting type: slide-in, can be marked with: THERMOFOX

Insert label - MM-EMT (EX18)R C1 WH/BK - 0803968



Insert label, continuous, cassette, white with black imprint, mounting type: slide-in, can be marked with: THERMOFOX

Thermal transfer printer set - THERMOFOX SET - 0803986

Accessories

Insert label - MM-EMT (EX23)R C1 WH/BK - 0803969



Insert label, continuous, cassette, white with black imprint, mounting type: slide-in, can be marked with: THERMOFOX

Label - MM-EML (EX10)R C1 WH/BK - 0803970



Label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label - MM-EML (EX12)R C1 WH/BK - 0803971



Label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label - MM-EML (EX18)R C1 WH/BK - 0803972



Label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label - MM-EML (EX24)R C1 WH/BK - 0803973



Label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Thermal transfer printer set - THERMOFOX SET - 0803986

Accessories

Label - MM-EML (EX10)R C1 SR/BK - 0803974



Label, continuous, cassette, silver with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label - MM-EML (EX12)R C1 SR/BK - 0803975



Label, continuous, cassette, silver with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label - MM-EML (EX18)R C1 SR/BK - 0803976



Label, continuous, cassette, silver with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label - MM-EML (EX24)R C1 SR/BK - 0803978



Label, continuous, cassette, silver with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Printing system accessories

Case - THERMOFOX/CASE - 0805002



Hard-top case for storing the THERMOFOX printer and accessory parts

Thermal transfer printer set - THERMOFOX SET - 0803986

Accessories

Case - THERMOFOX/BAG - 0805003



Shoulder bag for storing the THERMOFOX printer and accessory parts

Fastening clip - THERMOFOX/BELT CLIP - 0805004



Belt clip for fastening the THERMOFOX printer

Mounting unit - THERMOFOX/MAGNET HOLDER - 0805008



Magnetic holder for mounting the THERMOFOX printer on metal surfaces, e.g., on the control cabinet

Battery - THERMOFOX/ACCU - 0805009



Rechargeable battery for operating the THERMOFOX printer

Power supply unit - THERMOFOX/ADAPTER - 0805010



Power supply unit for operating the THERMOFOX printer

Shrink sleeve

Thermal transfer printer set - THERMOFOX SET - 0803986

Accessories

Shrink sleeve - MM-WMS 3,2 (EX5)R C1 WH/BK - 0803923



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 1.0 - 3.2 mm, can be marked with THERMOFOX

Shrink sleeve - MM-WMS 4,8 (EX9)R C1 WH/BK - 0803924



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 1.6 - 4.8 mm, can be marked with THERMOFOX

Shrink sleeve - MM-WMS 6,4 (EX10)R C1 WH/BK - 0803925



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 2.1 - 6.4 mm, can be marked with THERMOFOX

Shrink sleeve - MM-WMS 9,5 (EX16)R C1 WH/BK - 0803926



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 3.2 - 9.5 mm, can be marked with THERMOFOX

Shrink sleeve - MM-WMS-2 3,2 (EX5)R C1 WH/BK - 0803927



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 1.6 - 3.2 mm, can be marked with THERMOFOX

Thermal transfer printer set - THERMOFOX SET - 0803986

Accessories

Shrink sleeve - MM-WMS-2 4,8 (EX9)R C1 WH/BK - 0803928



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 2.4 - 4.8 mm, can be marked with THERMOFOX

Shrink sleeve - MM-WMS-2 6,4 (EX10)R C1 WH/BK - 0803929



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 3.2 - 6.4 mm, can be marked with THERMOFOX

Shrink sleeve - MM-WMS-2 9,5 (EX16)R C1 WH/BK - 0803930



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 4.8 - 9.5 mm, can be marked with THERMOFOX

Terminal marking

Label - MM-TML (EX4,2)R C1 TR/BK - 0803979



Label, continuous, cassette, transparent with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Label - MM-TML (EX9,5)R C1 TR/BK - 0803981



Label, continuous, cassette, transparent with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Thermal transfer printer set - THERMOFOX SET - 0803986

Accessories

Label - MM-TMT (EX6,35)R C1 WH/BK - 0803982



Label, continuous, cassette, transparent with black imprint, mounting type: snap-on, can be marked with THERMOFOX

Label - MM-TMT (EX9,5)R C1 WH/BK - 0803983



Label, continuous, cassette, white with black imprint, mounting type: snap-on, can be marked with THERMOFOX
