

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Sorti-box, equipped with TWIN ferrules in accordance with DIN 46228-4, CSA-certified, 20 pcs. of AI-TWIN 2x4-12 GY, 10 pcs. each of AI-TWIN 2x6-14 YE, AI-TWIN 2x10-14 RD

#### Why buy this product

- ☑ Color coding and the transparent cover facilitate fast access to the required ferrules
- Using the integrated euro-clip, they can be hung up on perforated board walls, for example, to save space
- The practical assortment boxes are designed to keep your workshop tidy



## **Key Commercial Data**

Packing unit	1 STK
GTIN	4 017918 947125
GTIN	4017918947125
Weight per Piece (excluding packing)	100.420 g
Custom tariff number	85369010
Country of origin	Germany

#### Technical data

#### General

Color	gray	
Components	free from silicone and halogen	
Flammability rating according to UL 94	НВ	
Material	E-CU	
Coating	tin-plated (galvanic)	

### Standards and Regulations

Connection in acc. with standard	CSA
Flammability rating according to UL 94	НВ

#### **Environmental Product Compliance**



## Technical data

## **Environmental Product Compliance**

China RoHS	Environmentally friendly use period: unlimited = EFUP-e	
	No hazardous substances above threshold values	

#### Articles in set

Ferrule - AI-TWIN 2X 4 -12 GY - 3201000



Ferrule, sleeve length: 12 mm, length: 23 mm, color: gray

#### Ferrule - AI-TWIN 2X 6 -14 YE - 3201013



Ferrule, sleeve length: 14 mm, length: 25 mm, color: yellow

#### Ferrule - AI-TWIN 2X10 -14 RD - 3201026



Ferrule, sleeve length: 14 mm, length: 26 mm, color: red

## Classifications

#### eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCI@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201
eCl@ss 8.0	27400218
eCl@ss 9.0	27400218

### **ETIM**

ETIM 2.0	EC000005



## Classifications

F-	ГΙ	п	м
_		ш	V

ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000524
ETIM 6.0	EC000524

#### **UNSPSC**

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	39121421

## Approvals

## Approvals

Approvals

CSA / CSAus / EAC / EAC / cCSAus

Ex Approvals

## Approval details

CSA	<b>SP</b>	http://www.csagroup.org/services-industries/product-listing/	247397
CSAus	<b>⊕</b> ° US	http://www.csagroup.org/services-industries/product-listing/	247397

EAC	EAC	EAC-Zulassung

	EAC	EAC	7500651.22.01.00246
--	-----	-----	---------------------



## Approvals

cCSAus



http://www.csagroup.org/us/en/services/ testing-and-certification/certified-product-listing

Phoenix Contact 2018 © - all rights reserved http://www.phoenixcontact.com