

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1733000106](#)
Status: **Active**
Overview: SpeedEdge™ Edge-Card and Mezzanine Connector System
Description: SpeedEdge Vertical Receptacle, 0.80mm Pitch, 5.60mm Height, 60 Circuits, UL94V-0, Black

Documents:

Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 1733000001-000 (PDF)	Product Literature (PDF)
Packaging Specification PK-70873-6002 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Receptacles
Series	173300
Application	Board-to-Board
Overview	SpeedEdge™ Edge-Card and Mezzanine Connector System
Product Literature Order No	987651-4151
Product Name	SpeedEdge
UPC	889056733632

Physical

Circuits (Loaded)	60
Circuits (maximum)	60
Color - Resin	Black
Flammability	94V-0
Glow-Wire Capable	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	0.978/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount
Unmated Height	5.60mm

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	250V AC

Material Info

Reference - Drawing Numbers



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[173300](#) Series

Mates With

SpeedEdge 60 Circuit Plug [173305-0115](#)

Application Specification
Electrical Model Document
Packaging Specification
Sales Drawing
Signal Integrity Report

1733000001-000
1733000006-000, 1733000008-000
PK-70873-6002
SD-173300-0100-001
1733000006-000, 1733000008-000

This document was generated on 03/29/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION