



Wiha SoftFinish® Pozidriv®



313 Pozidriv® Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
31305	0	60	2.4	3.0	.118	164	6.5	23	.91	.06	10
31310	1	80	3.1	4.5	.177	191	7.5	30	1.18	.11	10
31312	1	200	8.0	4.5	.177	311	12.3	30	1.18	.15	10
31315	2	100	3.9	6.0	.236	218	8.6	36	1.42	.20	10
31320	3	150	5.9	8.0	.315	274	10.8	41	1.61	.33	10

Wiha SoftFinish® Handle - Standard Series Sets



30299 20 Piece Slotted, Phillips, TORX®, Square & Pozidriv® Set

↓↔ lbs. 3.27

Item No.	Slotted:	Phillips:	TORX®:	Square:	Pozidriv®:
30299	3.0, 4.0, 5.5, 6.5, 8.0mm	0, 1, 2	T6, T8, T10, T15, T20, T25, T30	1, 2, 3	1, 2

Wiha SoftFinish® Slotted Spanner Nut Drivers



305 Slotted Spanner Nut Drivers, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	Size	mm	Inch	mm	mm	mm	Inch	mm	Inch	pkg.
30517	M1.7	80	3.1	0.5	4.0	184	7.2	23	.91	1
30520	M2	80	3.5	1.0	4.5	184	7.2	23	.91	1
30523	M2.3	90	3.5	1.0	5.0	201	7.9	30	1.18	1
30526	M2.6	100	3.9	1.2	5.5	201	7.9	30	1.18	1
30530	M3	100	3.9	1.2	6.0	211	8.3	30	1.18	1
30535	M3.5	100	3.9	1.4	7.0	218	8.6	36	1.42	1
30540	M4	100	3.9	1.4	8.0	218	8.6	36	1.42	1
30550	M5	125	4.9	2.0	10.0	243	9.6	36	1.42	1
30560	M6	125	4.9	2.5	11.0	243	9.6	36	1.42	1
30580	M8	150	5.9	3.0	14.0	274	10.8	41	1.61	1

Soft Grip BiCut SuperCut & Screwdriver Set



32644 7 Pc. Soft Grip BiCut SuperCut & Screwdriver Set

↕↔ lbs. 1.78

Item No.	BiCut SuperCut:
32644	8.0"/200mm BiCut SuperCut
	Screwdrivers: Phillips: #0, #1, #2
	Slotted: 3.0, 4.0, 6.5mm

Industrial BiCut SuperCut & Screwdriver Set




30942 7 Pc. Industrial BiCut SuperCut & Screwdriver Set

↕↔ lbs. 1.86

Item No.	BiCut SuperCut:
30942	8.0"/200mm BiCut SuperCut
	Screwdrivers: Phillips: #0, #1, #2
	Slotted: 3.0, 4.0, 6.5mm

Wiha SoftFinish® CushionGrip Drivers



30295 5 Piece Slotted & Phillips Screwdriver Set

Item No.	Slotted	Phillips	Size	mm	lbs.
30295	3.0	100	1	80	1.02
	4.0	100	2*	100	
	6.5	150			